




| REV | DESCRIPTION | BY | DATE | | | | |
|-----|-------------|-----|------|-----|-----|-----|-----|
| --- | --- | --- | --- | --- | --- | --- | --- |




TYPICAL BOX WITH INTERIOR




TYPICAL BOX SIDE VIEW



TYPICAL FRONT



TYPICAL MOUNTING OF EDB OR ECB-G3 BREAKERS



ENDWALL WITH KNOCKOUTS
(OTHER ENDWALL IS BLANK)

REFER TO DP CATALOG CLASS 1670 FOR ADDITIONAL INFORMATION

FOR NEMA TYPE 3R APPLICATIONS USE IN CONJUNCTION WITH PBA555

NF PANELBOARDS MEET THE APPLICABLE REQUIREMENTS OF UL AND CSA.

BOX: CODE GAUGE GALVANIZED STEEL. ONE ENDWALL IS BLANK, THE OTHER HAS KNOCKOUTS.

FRONT: MONO-FLAT CONSTRUCTION WITH CONCEALED TRIM SCREWS AND DOOR HINGES. ANSI 49 GRAY BAKED ENAMEL FINISH ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.

LOCK: FLUSH LOCK WITH BRUSHED, STAINLESS STEEL ESCUTCHEON. NSR-251 KEY.

DUAL DIMENSIONS: INCHES
MILLIMETERS

| MAXIMUM MAIN LUGS AMPERE RATING | MAXIMUM NUMBER OF CIRCUITS | H | | A | |
|---------------------------------|----------------------------|-------|------|-------|------|
| | | IN | MM | IN | MM |
| 250A | 18-30 | 68.00 | 1727 | 63.00 | 1600 |
| | 30-18 | 68.00 | 1727 | 63.00 | 1600 |
| | 30-30 | 80.00 | 2032 | 63.00 | 1600 |
| 250A WITH FEED THRU LUGS | 18-30 | 74.00 | 1880 | 69.00 | 1753 |
| | 30-18 | 74.00 | 1880 | 69.00 | 1753 |
| | 30-30 | 86.00 | 2184 | 69.00 | 1753 |
| 250A WITH SUB FEED BREAKERS | 18-30 | 80.00 | 2032 | 75.00 | 1905 |
| | 30-18 | 80.00 | 2032 | 75.00 | 1905 |
| | 30-30 | 92.00 | 2337 | 87.00 | 2210 |

| | |
|----------------------|--|
| JOB NAME: --- | EQUIPMENT DESIGNATION: --- |
| JOB LOCATION: --- | EQUIPMENT TYPE: NF 250A VERT MCB DOUBLE SPLIT BUS TYPE 1 |
| DRAWN BY: --- | DRAWING TYPE: --- |
| ENGR: --- | |
| DATE: SEPTEMBER 2017 | |
| DRAWING STATUS: --- | DWG# PBA871 |

