


L1200S  
NEMA TYPE 1  
NO KNOCKOUTS



CIRCUIT BREAKER TERMINAL LUG DATA						
CIRCUIT BREAKER CATALOG NO PREFIX	WIRING DIA	AMPERE RATING	CONDUCTORS PER POLE	WIRE SIZE (AWG/KCMIL)		TYPE
				MAX	MIN	
LGL - LLL	A B	300-600 700-1200	2	500	#2/0	AL OR CU

FACTORY INSTALLED GROUND KIT					
CATALOG NUMBER	MAXIMUM AMPERE RATING	NUMBER OF TERMINALS	WIRE SIZE (AWG/KCMIL)		TYPE
			MAX	MIN	
80104-403-01	-	7	350	#6	AL OR CU

DUAL DIMENSIONS: INCHES  
MILLIMETERS

FIELD INSTALLABLE CIRCUIT BREAKER DATA				
CIRCUIT BREAKER CATALOG NO PREFIX	WIRING DIA	AMPERE RATING	UL LISTED INTERRUPTING RATING RMS SYMMETRICAL AMPERES	
			500 Vdc NOM	50K
LLL	A B	300-600 700-1200	500 Vdc NOM	50K
LGL	A B	300-600 700-1200	600 Vdc MAX	20K

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
cULus LISTED - FILE E-136861  
THE SHORT CIRCUIT CURRENT RATING OF THIS ENCLOSED CIRCUIT BREAKER, INDICATED ON CHART ABOVE, MAY BE LESS THAN THE AIR RATING INDICATED ON THE INSTALLED CIRCUIT BREAKER.

CIRCUIT BREAKER ENCLOSURES  
300-1200 AMPERE  
NEMA/EEMAC TYPE 1 GENERAL PURPOSE ENCLOSURE  
SUITABLE ONLY FOR USE WITH UNGROUNDED UPS  
500 Vdc NOM 600 Vdc MAX



by Schneider Electric

DWG# PWCCB-ENCCB-0016  
NO.