



KNOCKOUTS				
SYMBOL	CONDUIT SIZE		HOLE DIA	
	IN	MM	IN	MM
A	.50	13	.87	22
B	.75	19	1.12	28
C	1.00	25	1.37	35
D	1.25	32	1.75	44
E	1.50	38	2.00	51
F	2.00	51	2.50	64
G	2.50	64	3.00	76
H	3.00	76	3.62	92



DUAL DIMENSIONS: INCHES MILLIMETERS

MAINS AMPERE RATING	FACTORY INSTALLED BYPASS TYPE	SHORT CIRCUIT CURRENT RATING	CATALOG NUMBER	SERIES	SPACES	MAXIMUM NUMBER OF SINGLE POLE QO CIRCUITS	LINE SIDE PHASE & NEUTRAL LUGS AWG/KCMIL	SERVICE GROUND LUG AWG/KCMIL	FEED THROUGH LUGS PHASE & NEUTRAL AWG/KCMIL
100	HORN	22K	QC816F100SH	M01	8	16	#6-350 CU/AL	#14-2/0 CU #12/2/0 AL	#6-300 CU/AL
125	NONE		QC816F125S						
	HORN		QC816F125SH						
150	NONE		QC816F150S						
	HORN		QC816F150SH						
200	NONE		QC816F200S						
	HORN	QC816F200SH							

NOTES:
 FINISH - GRAY BAKED ENAMEL POWDER COAT PAINT OVER CLEANED GALVANNEALED STEEL.
 MAXIMUM SYSTEM VOLTAGE: 120/240VAC, 1Ø3W, 50-60HZ, 208Y/120VAC, 1Ø3W, 50-60HZ (FROM A 3Ø4W SYSTEM)
 UL LISTED - FILE E-6294, VOL M
 SUITABLE ONLY FOR USE AS SERVICE EQUIPMENT.
 SUITABLE FOR UNDERGROUND/OVERHEAD SERVICE.

COMBINATION SERVICE ENTRANCE DEVICES RINGLESS TYPE METER MAIN QO 8-16 CIRCUIT FEED THROUGH RAINPROOF NEMA TYPE 3R ENCLOSURE SURFACE MOUNT ONLY	 SQUARE D by Schneider Electric
	DWG# PWFDS-SYRS-0047 NO.