



PB11299-35



1P

Circuit breakers			
Rating (In)	Curve B	Curve C	Curve D
6 A	EZ9F26106	EZ9F56106	-
10 A	EZ9F26110	EZ9F56110	-
16 A	EZ9F26116	EZ9F56116	-
20 A	EZ9F26120	EZ9F56120	-
25 A	EZ9F26125	EZ9F56125	-
32 A	EZ9F26132	EZ9F56132	-
40 A	EZ9F26140	EZ9F56140	-
50 A	-	EZ9F56150	-
63 A	-	EZ9F56163	-
Width in 9-mm modules	2		

PB11300-35



2P

Circuit breakers			
Rating (In)	Curve B	Curve C	Curve D
6 A	-	EZ9F56206	-
10 A	-	EZ9F56210	-
16 A	-	EZ9F56216	-
20 A	-	EZ9F56220	-
25 A	-	EZ9F56225	EZ9F86225
32 A	-	EZ9F56232	EZ9F86232
40 A	-	EZ9F56240	EZ9F86240
50 A	-	EZ9F56250	EZ9F86250
63 A	-	EZ9F56263	-
Width in 9-mm modules	4		

PB11301-35



3P

Circuit breakers			
Rating (In)	Curve B	Curve C	Curve D
6 A	-	EZ9F56306	-
10 A	-	EZ9F56310	-
16 A	-	EZ9F56316	-
20 A	-	EZ9F56320	-
25 A	-	EZ9F56325	EZ9F86325
32 A	-	EZ9F56332	EZ9F86332
40 A	-	EZ9F56340	EZ9F86340
50 A	-	EZ9F56350	EZ9F86350
63 A	-	EZ9F56363	EZ9F86363
Width in 9-mm modules	6		



PB11302-35



4P

Circuit breakers

Rating (In)	Curve B	Curve C	Curve D
6 A	-	EZ9F56406	-
10 A	-	EZ9F56410	-
16 A	-	EZ9F56416	-
20 A	-	EZ9F56420	-
25 A	-	EZ9F56425	-
32 A	-	EZ9F56432	-
40 A	-	EZ9F56440	-
50 A	-	EZ9F56450	-
63 A	-	EZ9F56463	-
Width in 9-mm modules	8		

PB114708-35



26970-25



Accessories

Screw shields

Set of 24 pieces (sealable)	EZ9A26982
-----------------------------	-----------

Padlocking device

Set of 2 pieces (sealable)	26970
----------------------------	-------

Certified compliant IEC/EN 60898-1

Additional feature

According to IEC/EN 60898-1


Breaking capacity (Icn)		
Ph/N	127 V AC	230 V AC
Ph/Ph	220 V AC	400 V AC
	10000 A	6000 A

Additional characteristics

Endurance (O-C)	Electrical	4,000 cycles
	Mechanical	10,000 cycles
Operating temperature	-25°C to +60°C	
Storage temperature	-40°C to +85°C	

Connection

DB406037



Rigid copper cables

6 to 25 A 1 to 25 mm² Tightening torque: 2 N.m

32 to 63 A 1 to 35 mm² Tightening torque: 3.5 N.m

Flexible copper cables

6 to 25 A 1 to 16 mm² Tightening torque: 2 N.m

32 to 63 A 1 to 25 mm² Tightening torque: 3.5 N.m

Note: Not suitable for external aluminium conductors