


KNOCKOUTS							
SYMBOLS	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64

QWIK GRIP SPACES CAPABILITY							
CABLE TYPE	10-3 FLAT	10-3 ROUND	10-2	12-3	12-2	14-3	14-2
W1	X	Y	X	X	X	X	X
W2	Y	X	Y	Y	X	Y	X
W3	X	X	Y	Y	X	Y	X
S1	X	X	X	X	Y	X	Y
S2	X	X	X	X	X	X	Y



QO124L125PQG
QO124L125PQGCV

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBERS	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO124L125PQG	120/240 VAC 1Ø 3W	125	24	34	#6-2/0
QO124L125PQGCV		125	24		#6-2/0

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.
LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
LOAD CENTERS WITH "P" IN CATALOG NUMBER INCLUDE EXTENDED NEUTRALS FOR PLUG ON NEUTRAL READY INTERIORS.
LOAD CENTERS WITH "Q" IN CATALOG NUMBER INCLUDE QWIK-GRIP CAPABILITIES.
LOAD CENTERS WITH "VP" IN CATALOG NUMBER INCLUDE SOME CIRCUIT BREAKERS IN PACKAGE.
LOAD CENTERS WITH "C" IN CATALOG NUMBER INCLUDE FLUSH/SURFACE MOUNTED COVER.

QO QWIK GRIP LOAD CENTER GENERAL PURPOSE
NEMA TYPE 1 ENCLOSURE INDOOR



DWG# PWFDS-SYRS-0147
NO.