



This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disassembled and at power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S et ne peuvent être utilisées ou divulguées à des tiers quels qu'ils soient sans son accord écrit. Seuls nos engagements pour l'exécution des plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte, démontés - débranchés - toutes sources coupées.

FUNCTIONAL PLATE V320U40-B0
VARIABLE SPEED DRIVE ATV320U40N4B
CATEGORIE 4, PL e/SIL3 ON STO FUNCTION AND LI3
WITH SECURITY MODULE PREVENTA XPS AV
POWER: 4 kW

FUNCTIONAL PLATE V320U40 VARIABLE SPEED DRIVE ATV320U40 POWER 4 KW				CELLEAN OFFER			
Echelle Scale		1/1					
Unite / Department							
Code diffusion Distribution code	Projet - No commande Project - Order No.			PHA1586303	Indice Rev 00	Folio Sheet 001	

00	16/01/2017	Edition originale / First issue	AKKA	O.MEURANT	A.PERRIN				
Ind	Date	Modification / Modification	Nom / Name	Visa	Nom / Name	Visa	Nom / Name	Visa	Archiv. Micro-filmed
Rev	Date		Dessine / Drawn	Verifie / Checked	Approuve / Approved				

	1	2	3	4	5	6	7	8	9	10
A	Folio Sheet	Designation Designation	Indice de modification Revision			Folio Sheet	Designation Designation	Indice de modification Revision		
	001	FRONT PAGE	00							
	002	SUMMARY	00							
	003	FUNCTIONAL PLATE	00							
	004	LAYOUT	00							
	005	WIRE LIST	00							
	006	PART LIST	00							
B										
C										
D										

This technical information is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in their position. Drawn out with separating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document (y compris les appareils, équipements, S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans le consentement écrit de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans son accord écrit. Seuls ceux autorisés par la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - toutes sources coupées.

Archivage
Microfilm

SUMMARY

CELLEAN OFFER




PHA1586303
 Project - No commande
 Project - Order No.
 Indice Rev 00
 Folio Sheet 002

This technical information is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans la autorisation écrite de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débrayés - débricolés - toutes sources coupées.

1 2 3 4 5 6 7 8 9 10



FUNCTIONAL PLATE
 V320U40
 VARIABLE SPEED DRIVE ATV320U40
 POWER 4 KW

CELLEAN OFFER



PHA1586303
 Project - No commande
 Project - Order No.

Indice Rev	Folio Sheet
00	003

This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document (y compris les appareils, les câbles, les accessoires, les schémas, les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - disjuncteurs - débrayés - toutes sources coupées.

1 2 3 4 5 6 7 8 9 10

A

B

C


D

A

B



C

D



APPROXIMATE WEIGHT : 5000 g

DO NOT DISCONNECT
THE GROUND WIRE
BEFORE DISCONNECTING
THE MOTOR CABLE



Rev	Date	Modification	Micro-filmed	Rev	Date	Modification	Micro-filmed
00	10/01/2017	First issue					

LAYOUT
V320U40
VARIABLE SPEED DRIVE ATV320U40
POWER 4 KW

CELLEAN OFFER



PHA1586303

Project - No commande Project - Order No.	Index Rev 00	Folio Sheet 004
--	--------------------	-----------------------

1			2		3		4	5	6	7	8	9	10
Type of circuit	Electrical Features		Wire Destination		Sheet N°	Designation	Color	Section	Wire Type	Câble end			
	P(kW)	I(A)	From	To						From	To		
POWER CIRCUIT	4 kW	13.7 A	XP1.1	Q1.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED		
			XP1.2	Q1.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED		
			XP1.3	Q1.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED		
			A1.M	MM1	003	UNIPOLAR INSULATED ELECTRIC CABLE	G/Y	10 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
CONTROL CIRCUIT			XAUX1.1	A1.STO	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.2	A1.P24	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.3	A1.DI1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.4	A1.DI2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.5	A1.DI3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.6	A1.R1A	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.7	A1.R1C	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
			XAUX1.8	A1.R1B	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED		
00			10/01/2017	First issue									
Rev	Date	Modification	Micro-filmed	Rev	Date	Modification	Micro-filmed						

This technical information remains the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those diagrams and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with separating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document (sauf la propriété exclusive de Schneider Electric Industries S.A.S. et ne pouvant être utilisées ou divulguées à des tiers) sont à des fins utiles qu'il s'agit sans son accord écrit. Seuls nos engagements sur ce schéma sont en position ouvert - débrayés - débrayés - toutes sources coupées.

WIRE LIST
 V320U40
 VARIABLE SPEED DRIVE ATV320U40
 POWER 4 KW

CELLEAN OFFER



PHA1586303
 Projet - No commande
 Project - Order No.

Indice Rev 00
 Folio Sheet 005

