

A

B

C

D

A

B



C

D

This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disassembled and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S et ne peuvent être utilisées ou divulguées à des tiers quels qu'ils soient sans son accord écrit. Seuls nos engagements pour l'exécution des plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte, démontés - débranchés - toutes sources coupées.

FUNCTIONAL PLATE V340D30-A0
VARIABLE SPEED DRIVE ATV340D30N4E
CATEGORIE 3, PLe AND IEC60204-1
ON STO FUNCTION AND DI1
WITH SECURITY MODULE PREVENTA XPS AV
POWER: 30 kW

FUNCTIONAL PLATE V340D30 VARIABLE SPEED DRIVE ATV340D30 POWER 30 KW				CELLEAN OFFER					
Echelle Scale 1/1									
Unite / Department		Code diffusion Distribution code		Projet - No commande Project - Order No.		Indice Rev 00		Folio Sheet 001	
00 16/01/2017 Edition originale / First issue		AKKA		O.MEURANT		A.PERRIN		PHA1619903	
Ind	Date	Modification / Modification	Nom / Name	Visa	Nom / Name	Visa	Nom / Name	Visa	Archiv. Micro-filmed
Rev	Date		Dessine / Drawn		Verifie / Checked		Approuve / Approved		

1	2	3	4	5	6	7	8	9	10		
Folio Sheet 001 002 003 004 005 006	Designation Designation FRONT PAGE SUMMARY FUNCTIONAL PLATE LAYOUT WIRE LIST PART LIST		Indice de modification Revision			Folio Sheet	Designation Designation		Indice de modification Revision		

A
 B
 C
 D

A
 B
 C
 D

This technical information constitutes the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties in any form without its written consent. Only those diagrams and drawings shown in this document are intended for execution. All devices shown in this document are shown in their normal position. Drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers ou à des tiers sans son accord écrit. Seuls les schémas et les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - débranchés - toutes sources coupées.

Archivage
Microfilm

SUMMARY

CELLEAN OFFER




PHA1619903

Project - No commande
Project - Order No.

Indice Rev 00	Folio Sheet 002
---------------------	-----------------------


This technical information, represented in this document, is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document (y compris les appareils, modules et accessoires Schneider Electric) ne peuvent être utilisées ou divulguées à des tiers (sous quelque forme que ce soit) sans son accord écrit. Seuls nos engagements pour l'exécution des plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - débranchés - toutes sources coupées.



FUNCTIONAL PLATE
V340D30
VARIABLE SPEED DRIVE ATV340D30
POWER 30 KW

CELLEAN OFFER




PHA1619903

Project - No commande Project - Order No.	Index Rev 00	Folio Sheet 003
--	--------------------	-----------------------

This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism discharged and all power sources off.



Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S et ne peuvent être utilisées ou divulguées à des tiers sans son accord écrit. Seuls nos engagements pour exécution, les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - toutes sources coupées.

1 2 3 4 5 6 7 8 9 10



APPROXIMATE WEIGHT : 44000 g

DO NOT DISCONNECT
THE GROUND WIRE
BEFORE DISCONNECTING
THE MOTOR CABLE



LAYOUT
V340D30
VARIABLE SPEED DRIVE ATV340D30
POWER 30 KW

CELLEAN OFFER

Schneider
Electric

PHA1619903

Projet - No commande
Project - Order No.

Indice
Rev
00

Folio
Sheet
004

1	2		3		4	5	6	7	8	9		10
Type of circuit	Electrical Features		Wire Destination		Sheet N°	Designation	Color	Section	Wire Type	Wire routing in cut out	Câble end	
	P (kW)	I (A)	From	To							From	To
POWER CIRCUIT	30 kW	66 A	----	Q1.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	ATOP	CABLE END INSULATED	CABLE END INSULATED
			----	Q1.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	ATOP	CABLE END INSULATED	CABLE END INSULATED
			----	Q1.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	ATOP	CABLE END INSULATED	CABLE END INSULATED
			Q1.2	A1.L1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	AMIDDLE CBOTTOM	CABLE END INSULATED	CABLE END INSULATED
			Q1.4	A1.L2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	AMIDDLE CBOTTOM	CABLE END INSULATED	CABLE END INSULATED
			Q1.6	A1.L3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	35 mm ²	H07V-K	AMIDDLE CBOTTOM	CABLE END INSULATED	CABLE END INSULATED
			A1.M	MM1	003	UNIPOLAR INSULATED ELECTRIC CABLE	G/Y	35 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
CONTROL CIRCUIT			XAUX1.1	A1.STOA	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.2	A1.STOB	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.3	A1.DI1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.4	A1.DI2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.5	A1.DI3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.6	A1.DI4	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.7	A1.DI5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED
			XAUX1.8	A1.+24	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm ²	H07V-K		CABLE END INSULATED	CABLE END INSULATED

This technical information remains in the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those diagrams and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document (sauf la propriété exclusive de Schneider Electric Industries S.A.S) et ne peuvent être utilisées ou divulguées à des tiers quels qu'ils soient sans son accord écrit. Seuls nos engagements par exécution les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - déarmés - débranchés - toutes sources coupées.

00	10/01/2017	Edition originale					
Ind.	Date	Modification	Archiv.	Ind.	Date	Modification	Archiv.

WIRE LIST
 V340D30
 VARIABLE SPEED DRIVE ATV340D30
 POWER 30 KW

CELLEAN OFFER



PHA1619903
 Project - No commande
 Project - Order No.

Indice Rev	Folio Sheet
00	005

