

This technical information, contained in this document is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans son accord écrit. Seuls nos engagements pour exécution, les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - toutes sources coupées.

Ind.	Date	Modification	Archiv.	Ind.	Date	Modification	Archiv.
00	27/02/2017	Edition originale					

FUNCTIONAL PLATE
 YD11
 SINGLE STAR DELTA MOTOR
 COORDINATION TYPE 2
 POWER: 11 kW

CELLEAN OFFER



OGH9360103		
Project - No commande	Index Rev	Folio Sheet
Project - Order No.	00	003

A

B

C

D

A


B

C

D



This technical information is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those diagrams and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document (sauf la propriété exclusive de Schneider Electric Industries S.A.S) et ne peuvent être utilisées ou divulguées à des tiers (sauf accord écrit) sans son accord écrit. Seuls nos engagements par exécution, les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - débranchés - toutes sources coupées.



APPROXIMATE WEIGHT : 2500 g

DO NOT DISCONNECT THE GROUND WIRE BEFORE DISCONNECTING THE MOTOR CABLE



Ind.	Date	Modification	Archiv.	Ind.	Date	Modification	Archiv.
00	27/02/2017	Edition originale					

LAYOUT
YD11
SINGLE STAR DELTA MOTOR
COORDINATION TYPE 2
POWER: 11 kW

CELLEAN OFFER



QGH9360103	
Projet - No commande	Indice
Project - Order No.	Rev
	00
Folio	Sheet
	004

1	2		3		4	5	6	7	8	9		10			
Type of circuit	Electrical Features		Wire Destination		Sheet N°	Designation	Color	Section	Wire Type	Wire routing in cut out	Câble end				
	P(kW)	I(A)	From	To							From	To			
POWER CIRCUIT	11 kW	22 A	XP1.1	Q1.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	/	CABLE END INSULATED LONG SIZE	CABLE END INSULATED			
			XP1.2	Q1.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K		CABLE END INSULATED LONG SIZE	CABLE END INSULATED			
			XP1.3	Q1.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K		CABLE END INSULATED LONG SIZE	CABLE END INSULATED			
						Q1.2	KM2.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM BTOP	CABLE END INSULATED	CABLE END INSULATED
						Q1.4	KM2.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM BTOP	CABLE END INSULATED	CABLE END INSULATED
						Q1.6	KM2.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM BTOP	CABLE END INSULATED	CABLE END INSULATED
						KM2.2	XP2.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM CTOP	CABLE END INSULATED	CABLE END INSULATED
						KM2.4	XP2.2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM CTOP	CABLE END INSULATED	CABLE END INSULATED
						KM2.6	XP2.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	ABOTTOM CTOP	CABLE END INSULATED	CABLE END INSULATED
						XP2.4	KM3.6	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	BTOP BBOTTOM	CABLE END INSULATED	CABLE END INSULATED
						XP2.5	KM3.4	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	BTOP BBOTTOM	CABLE END INSULATED	CABLE END INSULATED
						XP2.6	KM3.2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	4 mm²	H07V-K	BTOP BBOTTOM	CABLE END INSULATED	CABLE END INSULATED
CONTROL CIRCUIT			XAUX1.1	Q1.13	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	/	CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.2	KM1.A2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K		CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.3	Q1.23	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K		CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.4	Q1.24	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	/	CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.5	KM1.54	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K		CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.6	KM1.53	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	/	CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.7	KM2.21	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K		CABLE END INSULATED	CABLE END INSULATED			
			XAUX1.8	KM3.13	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	/	CABLE END INSULATED	CABLE END INSULATED			
			XT1.1	Q1.14	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K		CABLE END INSULATED	CABLE END INSULATED			
			XT1.2	KM2.13	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	/	CABLE END INSULATED	CABLE END INSULATED			

This technical information remains the property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans le consentement écrit de Schneider Electric Industries S.A.S. Les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - débrayés - toutes sources coupées.

WIRE LIST
YD11
SINGLE STAR DELTA MOTOR
COORDINATION TYPE 2
POWER: 11 kW

CELLEAN OFFER



OGH9360103
Projet - No commande
Project - Order No.
Indice Rev 00
Folio Sheet 005

		1	2	3	4	5	6	7	8	9	10
A	This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disengaged and all power sources off.	TAG	SHEET	DESCRIPTION			MANUFACTURER		MANUFACTURER REF.		QTY
		KM1	003	MECH INTERLOCK FOR TESYS LC1D			SCHNEIDER ELECTRIC		LAD9V2		1
		KM1	003	FRONT CONTACTS BLOCK. 2NO+2NC			SCHNEIDER ELECTRIC		LADN22		1
		KM1	003	CONT 25A 24VDC			SCHNEIDER ELECTRIC		LC1D25BD		1
		KM2	003	CONT 25A 24VDC			SCHNEIDER ELECTRIC		LC1D25BD		1
		KM3	003	STARDELTA KIT			SCHNEIDER ELECTRIC		LAD93217		1
		KM3	003	CONT 25A 24VDC			SCHNEIDER ELECTRIC		LC1D25BD		1
		Q1	003	MOTOR CIRCUIT BREAKER			SCHNEIDER ELECTRIC		GV2P22		1
		Q1	003	FRONT INST AUX CONTACTS NO +			SCHNEIDER ELECTRIC		GVAE20		1
		B	This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disengaged and all power sources off.	XAUX1	003	MOVING CONNECTOR SINGLE 8P 12A			SCHNEIDER ELECTRIC		LGYDC8APM
XP1	003			MOVING CONNECTOR 3P 32A			SCHNEIDER ELECTRIC		LGYDC3P32M2S		1
XP2	003			END BRACKET SNAP ON FOR 35 MM DIN RAILS			SCHNEIDER ELECTRIC		NSYTRAAB35		1
XP2	003			MARKING FOR TERMINAL BLOK NUMBER 1-10			SCHNEIDER ELECTRIC		NSYTRAB610		1
XP2	003			END COVER FOR NSYTRV22-TRV62-TRV102 TERMINALS			SCHNEIDER ELECTRIC		NSYTRAC22		1
XP2	003			SCREW TERMINAL BLOCK, 4mm2, 32A, SINGLE-LEVEL 1x1 SCREW, GREY			SCHNEIDER ELECTRIC		NSYTRV42		6
XT1	003			END BRACKET SNAP ON FOR 35 MM DIN RAILS			SCHNEIDER ELECTRIC		NSYTRAAB35		1
XT1	003			MARKING FOR TERMINAL BLOK NUMBER 1-10			SCHNEIDER ELECTRIC		NSYTRAB510		1
XT1	003			END COVER FOR NSYTRR23-NSYTRR22SC-NSYTRP23 TERMINALS			SCHNEIDER ELECTRIC		NSYTRACR23		1
XT1	003			SPRING TERMINAL BLOCK, 2.5mm2, 24A, SINGLE-LEVEL 1x2 SPRING, GREY			SCHNEIDER ELECTRIC		NSYTRR23		4
C	Les informations techniques contenues dans ce document (such as the appraisals, evaluations, Schneider Electric Industries S.A.S et ne peuvent être utilisées ou divulguées à des tiers (unless or divulgués à des tiers) sans son accord écrit. Tous nos engagements sur ce schéma sont en fonction de nos "conditions" - "conditions" - "conditions" - toutes sources coupées.			FUNCTION PLATE H200 x W300 6 WINDOWS VERSION A			SCHNEIDER ELECTRIC		NSYME02036A		1
				DIN RAIL, WIDTH: 35mm, HEIGHT: 15mm, LENGTH: 300mm			-----		DIN RAIL T3		1
				SHUTTER AND CABLE GLAND			SCHNEIDER ELECTRIC		NSYMEWGL		4
D	Les informations techniques contenues dans ce document (such as the appraisals, evaluations, Schneider Electric Industries S.A.S et ne peuvent être utilisées ou divulguées à des tiers (unless or divulgués à des tiers) sans son accord écrit. Tous nos engagements sur ce schéma sont en fonction de nos "conditions" - "conditions" - "conditions" - toutes sources coupées.										
00	27/02/2017	Edition originale / First issue									
Ind. Rev	Date	Modification /	Modification	Archiv. Micro-fimed	Ind. Rev	Date	Modification /	Modification	Archiv. Micro-fimed		
				PART LIST YD11 SINGLE STAR DELTA MOTOR COORDINATION TYPE 2 POWER: 11 kW				CELLEAN OFFER		Schneider Electric	
										OGH9360103	
										Project - No commande Project - Order No.	
										Indice Rev 00	
										Folio Sheet 007	