

MGE Galaxy 5000

20/30/40/60/80/100/120 kVA

The recommended power protection for all critical applications.



20 – 120 kVA state-of-the-art, three-phase power protection designed to meet a wide range of requirements from medium data centers to industrial and facilities applications.

- Upgradable power ranges
- Internal maintenance bypass
- Intuitive monitoring
- Parallel capable
- Front access servicing
- High power availability

Features and benefits

Flexible, three-phase power protection designed to meet a wide range of requirements, from medium data centers to industrial and facilities applications.

The MGE Galaxy™ 5000 offers state-of-the-art technology that increases performance and reliability, protecting against all power quality disturbances while allowing you to customize a solution to meet your unique specifications. The space-saving, reduced footprint, power factor corrected input (to prevent oversizing cables), circuit breakers, and generator result in lower total cost of ownership and overall customer savings. Upstream harmonics management allows a generator-friendly installation and flexible configurations for even the most demanding designs. Features such as parallel capability for both capacity and redundancy, full front access for ease of serviceability, user-friendly graphical display with multiple language options, and SNMP with network-based power management options make the Galaxy 5000 one of the easiest UPS units in its class to manage and maintain.

MGE Galaxy 5000

High-power availability

Fault tolerance Built-in 100 percent rated static bypass switch prevents interruption by allowing load transfer to utility power during heavy overloads

Redundant components Provides increased backup for greater reliability and ensures continuous operation

High overload capacity Improves downstream circuit discrimination

Installation and serviceability

Easy to install All connections are made through the front, eliminating the need for rear or side access

Front access servicing Simplifies installation and maintenance while minimizing space requirements

Multiple levels of service With package or individual service component options, our services are structured for you to choose what APC™ by Schneider Electric™ can do for you

Flexible and upgradeable

Expandable power ranges Scalable power levels to accommodate varying power requirements

Higher capacity or redundancy Parallel up to six modules to adapt to increasing power needs

Simple integration Easily works with networking and monitoring systems

Extended backup options Choice of backup times from five minutes to eight hours to meet varying requirements

Compatible Operates with inductive and leading power factor loads

Field upgradeable Change from single to parallel capability, increasing total power capacity, by simultaneously using multiple UPS units

Low total cost of ownership

Power factor corrected input Prevents the need for oversizing cables, circuit breakers, and generators

Efficient Up to 93 percent in online double conversion mode



MGE Galaxy 5000 features



1 IGBT based technology for power quality

Supplies clean, stable power to sensitive loads, ensuring critical power protection, optimum performance, and extended life

2 Dual input

Allows for connection to two separate input sources for increased availability

3 Parallel operation

Connect as many as six units in parallel for capacity and redundancy to grow with your power requirements

4 Redundant components

Provides increased backup for greater reliability and ensures continuous operation

5 Built-in static and maintenance bypass

Enables the UPS to transfer the load to utility power, without interruption, in the event of heavy overload or fault

MGE Galaxy 5000 options

Integrating input isolation transformer

The MGE Galaxy 5000 can be equipped with an input isolation transformer, fully integrating into the core module. Integrating the transformer directly into the module saves footprint and provides all the benefits of galvanic isolation — including providing a very robust buffer between the utility and the critical load.

Options

- Parallel system bypass cabinets
- IP32-rated cabinets
- External maintenance bypass
- Wall-mounted or stand-alone
- Remote alarm status panel (RASP)
- Remote summary alarm panel (RSAP)
- 42-pole distribution in a matching cabinet
- Top cable entry cabinet
- Communications cards
- Advanced power management software



StruxureWare for Data Centers Software Suite

APC by Schneider Electric UPS units and secure power systems are a core component of any architecture designed for highly critical applications, such as data centers, industry environments, infrastructure, and buildings.

Intelligent energy management of these systems is enabled by Schneider Electric EcoStruxure™ integrated hardware and software system architecture. StruxureWare™ software applications and suites are a key element of the EcoStruxure architecture. The software helps maximize system reliability and optimize operational efficiency.

StruxureWare for Data Centers software collects and manages real-time information about assets, resource use, and operation status throughout the data center life cycle. This data center infrastructure management (DCIM) software fully integrates the Galaxy 5000 UPS. With full system visibility, managers can monitor and apply this information in order to optimize data center performance to meet IT, business, and service-oriented goals.



A Comprehensive Portfolio of Services

Schneider Electric Critical Power & Cooling Services (CPCS) provides the highest quality services and solutions by trained and trusted professionals. Our world-class services offer a smart way to build, operate, and maintain your critical applications, ensuring the right people, in the right place, at the right time.

Assembly and Start-Up Service

Assembly and Start-Up Service by a certified Field Service Engineer (FSE) ensures full factory warranty coverage. A Schneider Electric-certified installation ensures your equipment is properly and safely configured for optimal performance. This service features a standard eight-hour, five-day response time, with upgrades available for off-business hours.

On-site Warranty Extension Service

In the event of a system issue, an FSE will arrive by the next business day (or faster with upgrades) to isolate, diagnose, and correct the problem in as little time as possible, minimizing downtime.

Advantage Plans

Flexible service packages offer hassle-free system maintenance to improve uptime at a predictable cost. The Advantage Plus, Prime, Ultra, and Max are full-service packages that include technical support, preventive maintenance, quick on-site response, and remote monitoring. Response time upgrades are available.

Remote Monitoring Service (RMS)

RMS is an economical and easy-to-use Web-based service that lets you quickly respond to environmental or system changes. Trained technicians provide secure 24-hour monitoring of your physical infrastructure to diagnose and resolve problems before they become critical.

Preventive Maintenance

Preventive Maintenance on-site examinations of your critical systems are designed to prevent problems and keep your system running at maximum efficiency.



Technical specifications

Rated power (kVA/kW)	20/18	30/27	40/36	60/54	80/72	100/90	120/108
Normal AC supply input							
Input voltage (V)	250 V ¹ to 470 V, three-phase						
Normal and bypass AC inputs	Separate						
Frequency (Hz)	45–66 HZ						
Input power factor	>.99						
THDI	<5% full load			<3% full load			
Bypass AC input							
Input voltage range	(380 V, 400 V, 415 V) +/- 10%						
Frequency	50 Hz/60 Hz +/- 10%						
Output							
Phase to phase output voltage (V)	380/400/415 V, three-phase + neutral						
Load power factor	0.9						
Output frequency	50 or 60 Hz +/- 0.1%						
Overload capacity utility operation	125% for 10 minutes; 150% for 60 seconds						
Output voltage regulation	+/- 1%						
Voltage distortion(THD)	<2% Phase-to-phase and Phase-to-neutral for non-linear loads						
Output voltage tolerance	+1% static, +/- 2% at 100% load step						
Overall efficiency							
Efficiency at full load (AC-AC)	87%	90%	92%				>93%
ECO mode	up to 97% ²						
Communication and management							
Control panel	Multifunction LCD, status, and control console						
Dimensions and weights							
UPS without battery (H x W x D)	1,900 x 712 x 850 mm						
UPS with internal battery (H x W x D)	1,900 x 1,112 x 850 mm						
Weight in kg (UPS without battery or with built-in battery)	400 kg min. 2748 kg max.						
Battery cabinet 700 mm (H x W x D)	1,900 x 712 x 850 mm, weight 135 kg						
Battery cabinet 1000 mm (H x W x D)	1,900 x 1,012 x 850 mm, weight 150 kg						
Auxillary cabinet 700 mm (H x W x D)	712 x 1,900 x 848 mm, weight 135 kg min. 150 kg max.						
Auxillary cabinet 1000 mm (H x W x D)	1012 x 1,900 x 848 mm, weight 135 kg min. 150 kg max.						
Auxillary cabinet 700 mm with isolation transformer (H x W x D)	712 x 1,900 x 848 mm, weight 118 kg min. 527 kg max.						
Auxillary cabinet 1000 mm with isolation transformer (H x W x D)	1,012 x 1,900 x 848 mm, weight 118 kg min. 527 kg max.						
Parallel system bypass cabinet (H x W x D)	1,000 x 800 x 303 mm min. 1900 x 1010 x 850 mm max. weight 71 kg min. 280 kg max.						
Regulatory							
Safety	ISO9001						
EMC/EMI/RFI	IEC 62040, IEC 62040-1-2, IEC 62040-3						
Approvals	CE, TUV, GOST						
Environmental							
Operating temperature	0–40 degrees C						
Storage temperature	0–40 degrees C						
Relative humidity	0–95% non-condensing						
Operating elevation	0–1,000 metres						
Storage elevation	0–12,000 metres						
Max. audible noise at 1 m from unit	< 66 dBA					< 63 dBA	

¹ Depending on load level; ² Only available in unitary products