

# PowerTag

## Selection guide\*

### PowerTag Acti9



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9</b>					
<b>Circuit breakers</b>					
iC60/iK60/DT60	Top	☑	-	-	-
	Bottom	☑	-	-	-
iC60 (double terminal)	Top	-	-	-	☑
	Bottom	-	-	-	☑
iC40	Top	-	☑	-	-
	Bottom	-	☑	-	-
DT40/iDPN/C40	Top	-	☑	-	-
	Bottom	-	☑	-	-
iC65N-K (China) iC65 (China)	Top	☑	-	-	-
	Bottom	☑	-	-	-
iDPN (China)	Top	-	☑	-	-
	Bottom	-	☑	-	-
iKQ (1P+W PowerTag on each pole)	Top	NA	-	-	-
	Bottom	☑ (1P+W only)	-	-	-
N40	Top	-	☑	-	-
	Bottom	-	☑	-	-
Reflex iC60	Top	☑	-	-	-
	Bottom	☑	-	-	-
Reflex XC40	Top	☑	-	-	-
	Bottom	-	-	-	☑ (1)
C32/C45/C60/C65/K60/T60/ C60-OEM	Top	☑	-	-	-
	Bottom	☑	-	-	-
<b>Circuit breakers equipped with Vigi module</b>					
iC60/iC65/iC60/iC65N-K with Vigi module	Top	☑ (CB)	-	-	-
	Bottom	-	-	-	☑ (Vigi) (1)
iC40 with Vigi iCG40	Top CB	-	☑ (CB)	-	-
	Top (Vigi)	-	☑ (Vigi 1P+N)	-	-
	Bottom (Vigi)	-	-	-	☑ (Vigi 3P+N)
iC40 with "outgoer" Vigi module	Top	-	☑ (CB)	-	-
	Bottom	-	-	-	☑ (Vigi)
DT40/DPN/C40 with "group feeder" Vigi module	Top CB	-	☑ (CB)	-	-
	Top Vigi	-	☑ (Vigi 1P+N)	-	☑ (Vigi 3P+N)
DT40/DPN/C40 with "outgoer" Vigi module	Top	-	☑ (CB)	-	-
	Bottom	-	-	-	☑ (Vigi)
DT60 with Vigi TG60	Top CB	☑ (CB) only A9MEM1541	-	-	-
	Top Vigi	-	-	-	☑ (Vigi) (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

## Selection guide\* (cont.)



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9</b>					
<b>Residual current devices</b>					
iID/iID K	Top	✓	-	-	-
	Bottom	✓	-	-	-
iID (double terminal)	Top	-	-	-	✓
	Bottom	-	-	-	✓
iID40	Top	-	✓ 1P+N	-	✓ 3P+N
	Bottom	✓	-	-	-
iDPN Vigi "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
iC60H RCBO/iC60H2 RCBO/ IKQE RCBO	Top	NA (fishbone)	-	-	-
	Bottom	-	-	✓	-
iC60 RCBO	Top	✓	-	-	-
	Bottom	✓	-	-	-
iCV40 "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
iCV40 "outgoer" 3P+N	Top	-	✓	-	-
	Bottom	-	-	-	✓
DPN Vigi/DT40 Vigi/C40 Vigi "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
DPN Vigi/DT40 Vigi/C40 Vigi/ iDPN Vigi "outgoer" 3P+N	Top	-	✓	-	-
	Bottom	-	-	-	✓
DPN Vigi K	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
N40 Vigi "outgoer"	Top	-	✓	-	-
	Bottom	-	✓	-	-
iDc/ITG40/C40	Top Left	-	✓	-	-
	Top Right	-	✓	-	-
DCP Vigi	Top	✓	-	-	-
	Bottom	✓	-	-	-
C60H RCBO (Multi9)	Top	NA (fishbone)	-	-	-
	Bottom	-	-	✓	-
ID ≤ 63 A ID Type B ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
RED/REDS/REDTest	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

## Selection guide\* (cont.)

### PowerTag Acti9







Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9</b>					
<b>Switches</b>					
iSW ≤ 63 A	Top	<input checked="" type="checkbox"/>	-	-	-
	Bottom	<input checked="" type="checkbox"/>	-	-	-
iSW-NA ≤ 63 A	Top	<input checked="" type="checkbox"/>	-	-	-
	Bottom	<input checked="" type="checkbox"/>	-	-	-
iSW 20/32 A	Top	-	-	-	<input checked="" type="checkbox"/>
	Bottom	-	-	-	<input checked="" type="checkbox"/>
i-NA ≤ 63 A	Top	<input checked="" type="checkbox"/>	-	-	-
	Bottom	<input checked="" type="checkbox"/>	-	-	-
<b>Fuse disconnectors</b>					
STI	Top	-	<input checked="" type="checkbox"/>	-	-
	Bottom	-	<input checked="" type="checkbox"/>	-	-
SBI 14x51/SBI 22x58 ≤ 63 A	Top	-	-	-	<input checked="" type="checkbox"/> (1)
	Bottom	-	-	-	<input checked="" type="checkbox"/> (1)
D01/D02	Top	-	-	-	<input checked="" type="checkbox"/> (1)
	Bottom	-	-	-	<input checked="" type="checkbox"/> (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

## Selection guide\* (cont.)

			PowerTag NSX			
						
Products (AC network)		Mounting position	250 3P	250 3P+N	630 3P	630 3P+N
<b>Compact</b>						
<b>Circuit breakers</b>						
<b>NSX100/160/250 B/F/N/H/S/L/R Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NSX400/630 F/N/H/S/L/R Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NSX100/160/250 B/F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (2)	-	-
<b>NSX400/630 F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top / Bottom	-	-	☑ (3)	-
	4P	Top / Bottom	-	-	-	☑ (2) (3)
<b>NS100/160/250 N/ SX/H/L Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NS400/630 N/H/L Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NS100/160/250 N/ SX/H/L Plug-In (mounted on the base)</b>	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (2)	-	-
<b>NS400/630 N/H/L Plug-In (mounted on the base)</b>	3P	Top / Bottom	-	-	☑ (3)	-
	4P	Top / Bottom	-	-	-	☑ (2) (3)
<b>Circuit breakers equipped with Vigi block</b>						
<b>NSX100/160/250 B/F/N/H/S/L/R Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NSX400/630 F/N/H/S/L/R Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NSX100/160/250 B/F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top	☑	-	-	-
<b>NSX400/630 F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top	-	-	☑ (3)	-
<b>Switches</b>						
<b>INS250/INV - 100/160/200/250</b>	3P	Bottom	-	☑	-	-
	4P	Top / Bottom	-	☑ (2)	-	-
<b>INS/INV - 320/400/500/630</b>	3P	Bottom	-	-	-	☑
	4P	Top / Bottom	-	-	-	☑ (2)

(2) neutral on the right when mounted on top side

(3) when plate mounted, need to add a 4 mm intercalary under the PowerTag module (see Compact NSX catalogue)

(\*) Refer to the product catalogue for technical characteristics

Complementary technical information

PowerTag

Selection guide\* (cont.)



Indice	Date	Modification	Name
2.4	20/08/2018	Remove C120 and NG125 products and add note (1)	Sonovision
2.3	5/04/2018	New table PowerTag NSX page 5	Sonovision
2.2	22/03/2018	Update PowerTag NSX (LV434020 - LV434021 - LV434022 - LV434023) images	Sonovision
2.1	22/02/2018	New tables	Sonovision
2.0	03/04/2017	New charte	Sonovision
1.0	22/03/2016	Creation	Sonovision