

Product data sheet

Characteristics

AEH-PV08-75W

Solar Panel 12V,75Wp



Main

Maximum power (P_{max})	75 Wp
Open circuit voltage (V_{oc})	22.46 V
Short circuit current (I_{sc})	4.24 A
Maximum voltage (V_{mp})	18.90 V
Maximum current (I_{mp})	3.97 A

Complementary Mechanical Specifications

Overall dimensions (L x B x H)	505 x 30 x 1005 mm
Net weight	8 Kg
Gross weight	9 Kg

Environment

Operating temperature	-40 to 85°C
Relative humidity	85%

Packaging Information

Type	Dimensions (L x B x H in mm)	Net weight (Kg)	Gross weight (Kg)	No. of units
Unitary package	700 x 50 x 1030	8	9	1
Group package	720 x 270 x 1050	40	45	5
Pallet package	1100 x 1050 x 890	180	200	20

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for, and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.