Product data sheet

Characteristics

EY56CSCxxx

Easy56TM Appliance Connectors

Ordering Details

Catalogue Number	Description
EY56CSC310	Appliance Connector 3 Pin Flat, 250V 10A
EY56CSC315	Appliance Connector 3 Pin Flat, 250V 15A



Overview

Schneider Electric's Easy56 Plug Extension Socket/ Appliance Connector is an important product. It provides a common unit for both cord extension socket and appliance connector applications.

Available in 10A and 15A, both connectors have impact resistant, UV stabilised mouldings. The IP66 rating can be achieved when extension socket/connectors are used in conjunction with compatible accessories such as EY56P Plugs and EY56AI Appliance Inlets. All are fitted with a screwed locking ring for securing to socket outlets and to ensure IP66 rating.

Another key feature of the Easy56 design is the transparent centre body section for instant visual checking of connections.

The plug extension sockets are also compatible with Clipsal 56 series accessories which provide further flexibility. This means if other amperages or voltages are required, it is recommended to refer to the Clipsal 56 series range.

Features

- Locking rings to ensure IP66 rating
- Transparent body to view cable connections
- Transparent pin surround to view pins during plug insertion/removal



Specifications

Voltage Rating	250V
Current Rating	10A, 15A
Dimensions	65 mm x 65 mm x 105 mm
Product weight	107g
Ambient air temperature for operation	-25 to 75 degrees Celsius
IP Rating to IEC 60529	66
Standards	AS/NZS 3120

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant
REACh	Compliant
Product environment profile	Available

Applications

Commercial and Industrial environments both indoors and outdoors where protection from dust, water, and UV is important.

Socket Configurations





10A 250V



15A 250V



Dimensions

EY56CSC310 EY56CSC315



