

AENOR

AENOR Product Certificate Low Voltage Material



030/002384

AENOR certifies that the organization

SCHNEIDER ELECTRIC ESPAÑA, S.A.

registered office CL BAC DE RODA, 52 08019 BARCELONA (España)

supplies Circuit-Breakers

in compliance with
UNE-EN 60898-1:2004 (EN 60898-1:2003)
UNE-EN 60898-1:2004/A11:2006 (EN 60898-1:2003/A11:2005)
UNE-EN 60898-1:2004/A1:2005 (EN 60898-1:2003/A1:2004)
UNE-EN 60898-1:2004/A12:2009 (EN 60898-1:2003/A12:2008)
UNE-EN 60898-1:2004/A13:2013 (EN 60898-1:2003/A13:2012)
UNE-EN 60947-2:2007 (EN 60947-2:2006)
UNE-EN 60947-2:2007/A1:2011 (EN 60947-2:2006/A1:2009)
UNE-EN 60947-2:2007/A2:2013 (EN 60947-2:2006/A2:2013)

References Specified in Annex to the Certificate

Production site PLOVDIV PLANT 4202 RADINOVO (Bulgaria)

Certification scheme In order to grant this Certificate, AENOR has tested the product and has verified the quality system implemented for its manufacture. AENOR performs these tasks periodically while the Certificate has not been cancelled, in accordance with Specific Rules RP 030.15.

This certificate supersedes 030/002384, dated 2015-03-27

First issued on 2015-03-13
Modified on 2017-03-06
Validity date 2020-03-13

Avelino BRITO
General Manager

Original Electrónico

AENOR

AENOR Product Certificate Low Voltage Material

030/002384

Annex to Certificate

Trade mark: Schneider Electric

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F79106	1P	230/400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79110	1P	230/400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79116	1P	230/400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79120	1P	230/400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79125	1P	230/400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79132	1P	230/400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79140	1P	230/400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79206	2P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79210	2P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79216	2P	400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79220	2P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79225	2P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79232	2P	400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79240	2P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79306	3P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79310	3P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79316	3P	400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79320	3P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79325	3P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79332	3P	400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79340	3P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79406	4P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79410	4P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79416	4P	400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79420	4P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79425	4P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79432	4P	400 V-	32 A	6000 A	C	10 kA	7,5 kA

First issued on 2015-03-13
Modified on 2017-03-06
Validity date 2020-03-13

Original Electrónico

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com

AENOR

AENOR Product Certificate Low Voltage Material

030/002384

Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F79440	4P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79606	1P+N	230 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79610	1P+N	230 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79616	1P+N	230 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79620	1P+N	230 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79625	1P+N	230 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79632	1P+N	230 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79640	1P+N	230 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F89106	1P	230/400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89110	1P	230/400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89116	1P	230/400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89120	1P	230/400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89125	1P	230/400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89132	1P	230/400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89140	1P	230/400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89206	2P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89210	2P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89216	2P	400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89220	2P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89225	2P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89232	2P	400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89240	2P	400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89306	3P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89310	3P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89316	3P	400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89320	3P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89325	3P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89332	3P	400 V-	32 A	10000 A	C	15 kA	7,5 kA

First issued on 2015-03-13
Modified on 2017-03-06
Validity date 2020-03-13

Original Electrónico

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com

AENOR

AENOR Product Certificate Low Voltage Material

030/002384

Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F89340	3P	400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89406	4P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89410	4P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89416	4P	400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89420	4P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89425	4P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89432	4P	400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89440	4P	400 V-	40 A	10000 A	C	15 kA	7,5 kA

First issued on 2015-03-13
Modified on 2017-03-06
Validity date 2020-03-13

Original Electrónico

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com