

# Certificate



Intertek

for European Product Safety


Reference No. 1415295

## Junction box

Type designation	TB32/42, TB77/SH53, TB50/SH26, 60/46
Certificate holder	<b>Schneider Electric Sverige AB</b> <b>CMS product department</b> <b>Tillverkarvägen 2</b> <b>611 29 Nyköping</b> <b>SWEDEN</b>
The product complies with the standard(s)	EN 60670-1:2005+A1:2013 EN 60670-21: 2007
Date of expiry	17 December 2019
EU Directive information	The product satisfies the provisions for CE marking according to the Low Voltage Directive 2006/95/EC.

Additional information in Appendix.

Certification Body Intertek Semko AB, Product Certification Place Kista - Stockholm

Signed   
David Haglund Date 17 December 2014  
Page 1 of 3

This certificate is issued in accordance with the terms and conditions set out in the Appendix.

**Intertek  
Appendix**

Reference No. 1415295

*Technical data**Type designation*

60/46

*Standard sheet*

SS 430 06 17

*Trade mark***Schneider**  
Electric*Product information*

Circular flush mounting box for accessory, for post mounting with inlets for 16 mm corrugated conduit. Temperature range -25/+90°C.

Material content of the box:

No halogen according to EN 50267-2-2:1999.

*Type designation*

TB 32/42, TB 50/SH26, TB 77/SH53

*Standard sheet*

SS 430 06 19

*Trade mark***Schneider**  
Electric*Product information*

Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Alternative design with fire protective pad only for types TB 32/42 and TB 50/SH26.

Boxes with cc 70 mm.

Type TB 32/42 with inner depth of 26 mm.

Type TB 50/SH26 with inner depth of 44 mm.

Type TB 77/SH53 with inner depth of 104 mm.

Temperature range -25/+90°C.

Material content of the boxes:

No halogen according to EN 50267-2-2:1999.

*This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.*

**Intertek  
Appendix**

Reference No. 1415295

*Manufacturing site(s)*

Minera AS  
Runninveien 27  
2150 Årnes  
NORWAY

Thorsman & Co AB  
Tillverkarvägen 2  
611 29 Nyköping  
SWEDEN

Elda-Eltra Elektrotechnika S.A.  
ul. Bugno 1  
PL-78-400 Szczecinek  
POLAND

This certificate, which includes production control, constitutes sufficient support for an EC Declaration of Conformity and CE marking, according the principle of presumption of conformity, of the products according to the Low Voltage Directive 2006/95/EC.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

This certificate replaces previously issued ref. No. 908281 dated 17 December 2009.  
A new certificate has been issued on account of renewal of S-certificate.

*Certification Body* Intertek Semko AB, Product Certification *Place* Kista - Stockholm

*Signed*

  
\_\_\_\_\_  
David Haglund

*Date* 17 December 2014

*This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.*