

Certificate



Intertek

for European Product Safety

Reference No. 1415312

Junction box

Type designation

BBV30428

Certificate holder

Schneider Electric Sverige AB
CMS product department
Tillverkarvägen 2
611 29 Nyköping
SWEDEN

The product complies with
the standard(s)

EN 60670-1:2005+A1:2013

Date of expiry

17 December 2019

EU Directive information

The product satisfies the provisions for CE marking according to the Low Voltage Directive 2006/95/EC.

Additional information in Appendix.


Certification Body

Intertek Semko AB, Product Certification

Place

Kista - Stockholm

Signed



David Haglund

Date

17 December 2014

Page 1 of 3

This certificate is issued in accordance with the terms and conditions set out in the Appendix.

**Intertek
Appendix**

Reference No. 1415312

Technical data

Type designation

BBV30428

Standard sheet

SS 430 06 18

Trade mark

Schneider
Electric

Product information

Circular flush connecting box (hollow wall mounting, 13-26 mm wall plate) for accessory of grey insulated material with inlets for 16 and 20 mm conduits and 2 knock-outs at the bottom for 16 and 20 mm conduits. Alternative design with fire protective pad. Temperature range -25/+90°C.

Material content of the box:

No halogen according to EN 50267-2-2:1999.

Type designation

BBV30428

Standard sheet

SS 430 06 18

Trade mark

ELKO

Product information

Circular flush connecting box (hollow wall mounting, 13-26 mm wall plate) for accessory of red insulated material with inlets for 16 and 20 mm conduits and 2 knock-outs at the bottom for 16 and 20 mm conduits. Alternative design with fire protective pad. Temperature range -25/+90°C.

Material content of the box:

No halogen according to EN 50267-2-2:1999.

Accessory for the box: Inlet socket for conduits, for separate mounting on the box.

Type: 20004330-double inlet 16/20 mm in grey.

Type: 20007217-double inlet 16/20 mm in red.

This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.

