

LICENCE

No. 19150 - Issue No 2

Issued to:
 Applicant:
Merten GmbH
Fritz-Kotz-Straße, 8
51674 WIEHL-BOMIG
Germany

Licensee:
Schneider Electric Industries SAS
35 Rue Joseph Monier
92506 RUEIL MALMAISON Cedex
France



Product : infra-red movement detector

Trade name(s) : MERTEN, SCHNEIDER ELECTRIC

Type(s)/model(s) : 5628 (Argus 220), 5651 (ARGUS 110 Basic), 5652 (ARGUS 220 Basic), 5654 (ARGUS 220 Connect), 5656 (ARGUS 220 Timer)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 382

SGS CEBEC hereby grants the right to use the CEBEC certification mark
 The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 04/05/2017

ir. C. Lana,
 Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
 This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	infra-red movement detector
Trade name(s)	:	MERTEN, SCHNEIDER ELECTRIC
Type(s)/Model(s)	:	5628 (Argus 220), 5651 (ARGUS 110 Basic), 5652 (ARGUS 220 Basic), 5654 (ARGUS 220 Connect), 5656 (ARGUS 220 Timer)
pattern no(s).	:	1
contact opening (gap)	:	micro-gap
method of mounting	:	surface type
cover	:	housing of thermoplastic material
terminals	:	screwless (rigid) terminals
rated voltage (Un)	:	230 Vac
kind of load	:	incandescent lamps, fluorescent lamps, declared load
design	:	enclosed
degree of protection	:	IP 55
method of actuating	:	proximity
additional information	:	switching device : mechanical switching device (relay)
markings	:	trade name, type indication, symbol of kind of load and electrical ratings on the housing

Product data - type 5628 (Argus 220)

rated current (In) : 10 AX

Product data - type 5651 (ARGUS 110 Basic)

rated current (In) : 16 A

Product data - type 5652 (ARGUS 220 Basic)

rated current (In) : 16 A

Product data - type 5654 (ARGUS 220 Connect)

rated current (In) : 16 A

Product data - type 5656 (ARGUS 220 Timer)

rated current (In) : 16 A

TESTS

Test requirements

NBN EN 60669-2-1 based on EN 60669-2-1:2004 + A1:2009 + A12:2010

Test results

The test results are laid down in certification file ref.612903/02

Remarks


This certificate is based on certificates ref. DE1-54022 & DE1-54513 and test reports ref. 5008062-1690-0005 & 202405-CC3-1

Conclusion

The examination proved that all test requirements were met.

Checked by, project leader : Luigi Zanutto - 04/05/2017

Department Manager,
Product Certification


2017-05-04

Certification Manager :

FACTORY LOCATION(S)

Lexel Fabrika, SIA
Krustpils 35a
1073 RIGA
Latvia