


# Flush mounting Mini Pragma (offer B)

1 row, 4 to 18 modules

2 and 3 rows, 12 modules per row



Connection assembly



13374



13942

## Function

Mini Pragma is a distribution or subdistribution enclosure up to 63 A. It is used indoors, in housing or the service sector, for new installations or renovation work.

## Description

### Technical data

- Equipped with an opaque or transparent, curved door:
  - 1 row: wicket door opens 90° upwards
  - 2 and 3 rows: door opens 180° to the right and to the left.
- Rated current of the enclosure:
  - 4 modules: 50 A
  - 6 to 36 modules: 63 A.
- Material:
  - colour: white RAL 9003.
- Compliance with standards:
  - complies with IEC 439.3 (EN 60-439-3).
- Degree of protection:
  - as in IEC 529: IP40 (protection against solids and liquids)
  - as in EN 50-102: IK07 (protection against mechanical impacts)
  - class 2 protection against indirect contact.
- Fire and excessive heat withstand capacity as in IEC 695-2-1:
  - enclosure: 650°C/30 s
  - N - earth terminal bar supports: 960°C/30 s.

### Composition

Flush mounting Mini Pragma is composed of:

- a symmetrical base:
  - robust
  - of a depth adapted to walls with a low thickness
  - with punch-outs for tube insertion on the 4 sides
- 1 to 3 symmetrical rails with adjustment of verticality:
  - 1 row: adjustable symmetrical rail depth
  - 2 and 3 rows: one-piece chassis enabling wiring outside the base
- a rigid, reversible front panel:
  - with a curved wicket door or curved door
  - equipped with blanking plates which can be punched-out.

### Accessories delivered with the enclosure

Flush mounting Mini Pragma is delivered equipped with:

- a circuit identification strip per row:
  - to be glued on the front panel
- a connection assembly:
  - 2 earth-neutral terminal blocks
  - 2 terminal block supports
- terminal block details :

Number of holes	Composition	
	10 <sup>□</sup>	16 <sup>□</sup>
4	2	2
8	4	4
16	8	8
22	11	11
32	16	16

## Catalogue numbers

Enclosure with door					
Number of rows	Capacity in modules		terminal blocks delivered (no. x no. holes)	Cat. no.	
	modules of 9 mm	modules of 18 mm		Opaque	Transparent
1	8	4	2 x 4	13371	13301
1	12	6	2 x 4	13372	13302
1	16	8	2 x 8	13373	13303
1	24	12	(2 x 4) + (2 x 8)	13374	13304
1	36	18	2 x 16	13375	13305
2	48	24	2 x 16	13932	13942
3	72	36	2 x 22	13933	13943

## Additional information

Optional accessories: page 93010

Dimensions: page 93900