



# ÖVE-CERTIFICATE

including the entitlement to use the Austrian Safety Mark



Certificate No.: **4900-046-08**

Valid from: 2019 07 09  
until: 2020 06 23

The Austrian Electrotechnical Association (OVE) hereby grants the right to the company mentioned below to label the listed products with the Austrian Safety Mark.

Company: **Schneider Electric Industries SAS**  
35, rue Joseph Monier  
92500 Rueil-Malmaison  
France

Product: **Two pole socket outlet with side earthing contacts**

The products submitted by the applicant were type tested in accordance with the requirements of the technical standards and specifications listed in this certificate. OVE certifies the conformity of the listed products and those products manufactured strictly identical to the submitted ones (EN ISO/IEC 17067, Conformity Assessment Scheme Type 5).

The manufacturing process and the products are subject to ongoing surveillance based on harmonized European procedures. This certificate has been issued under the presumption and conditional on the fact that the applicant holds all necessary legal rights with regard to the product, presented for the testing and certification.

Results of testing are shown in file No(s): **TGM-VA EE 33387C, TGM-VA EE 33387D**

**Österreichischer Verband für Elektrotechnik**  
Head of Testing and Certification

Digitally signed by W. Martin  
Email=w.martin@ove.at

Dipl.-Ing. W. Martin

Wien, 2019 07 09



## OVE Testing and Certification

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).



**Manufacturer:**

Merten GmbH  
Fritz Kotz Straße 8  
51674 Wiehl-Bomig  
Germany

**Factory location(s):**

Merten GmbH  
Fritz Kotz Straße 8  
51674 Wiehl-Bomig  
Germany

**Tested and certified according to:**

ÖVE/ÖNORM IEC 60884-1:2005-09-01  
ÖVE/ÖNORM E 8684-1:2010-03-01

**Product: Two pole socket outlet with side earthing contacts**

**Type designation:**

*Rating:*

**Trademark:**

**230**

Rated voltage: AC 250 V  
Rated current: 16 A  
SCHUKO socket-outlet  
screwless terminals, flush-type  
see typelist

MERTEN/SCHNEIDER ELECTRIC

**OVE Testing and Certification**

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

## Typelist

### System M (Thermo/Duro)

<b>230/2371</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert	MERTEN/SCHNEIDER ELECTRIC
<b>230/2373</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/2376</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with hinged lid	MERTEN/SCHNEIDER ELECTRIC
<b>230/2376 IP44</b> Rated voltage: AC 250 V Rated current: 16 A IP 44 Insert with hinged lid and gasket	MERTEN/SCHNEIDER ELECTRIC
<b>230/2374 IP44</b> Rated voltage: AC 250 V Rated current: 16 A IP 44 Insert with hinged lid and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/2374</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with hinged lid and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/2300</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/2300-35 (M-Creativ)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with transparent cover and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC

### OVE Testing and Certification

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

**230/2301** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Socket-outlet

**230/2309** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Central plate with labelling field and control light incl. Modul Mxx2003-0004

**230/2309** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with labelling field and improved protection against accidental contact

**230/2474** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with hinged lid and labelling field

**230/2485** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with improved protection against accidental contact

**230/2496** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with labelling field and improved protection against accidental contact

**230/2470 (Atelier-M)** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Socket-outlet

**230/2471 (Atelier-M)** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Socket-outlet with improved protection against accidental contact

**230/2472 (1-M)** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Socket-outlet

## OVE Testing and Certification

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

**230/2473 (1-M)**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with improved protection against accidental contact

**230/2334**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Central plate with light opening and LED display lighting incl. Modul Mxx2334

**230/2315**

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert lockable with hinged lid and improved protection against accidental protection

**System Design (Thermo/Duro)**

**230/2375**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert

**230/2377**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

**230/2372**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid

**230/2379**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field

**230/2378 IP44**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, gasket and improved protection against accidental contact

**OVE Testing and Certification**

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

**230/2378** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and improved protection against accidental contact

**230/2306** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact, Tracent

**230/2379** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field and control light (Modul Mxx2003-0004)

**230/2308** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field and improved protection against accidental contact

**230/2478** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and labelling field

**230/2476** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with improved protection against accidental contact

**230/2477** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with labelling field and improved protection against accidental contact

**System Design (Thermo/metal)**

**230/NHA5191702 (thermo)** MERTEN/SCHNEIDER ELECTRIC

**230/NHA5200102 (metal)**

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert

**OVE Testing and Certification**

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

<b>230/NHA2922902 (thermo)</b> <b>230/NHA2922002 (metal)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5191902 (thermo)</b> <b>230/NHA2922002 (metal)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Socket-outlet with labelling filed	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5191802 (thermo)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with Floor Light and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5195702 (thermo)</b> <b>230/NHA5195702 (metal)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with hinged lid and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5195702/PHA8168102 (thermo)</b> <b>230/NHA5195702/NHA5200202 (metal)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert with hinged lid and improved protection against accidental contact and labelling filed	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5195702 IP44 (thermo)</b> <b>230/NHA5195702 IP44 (metal)</b> Rated voltage: AC 250 V Rated current: 16 A IP 44 Insert with hinged lid, gasket and improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA2920902 (thermo)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert for special electric circuits with improved protection against accidental contact	MERTEN/SCHNEIDER ELECTRIC
<b>230/NHA5191902 (thermo)</b> Rated voltage: AC 250 V Rated current: 16 A IP 20 Insert for special electric circuits with improved protection against accidental contact and labelling filed	MERTEN/SCHNEIDER ELECTRIC

## OVE Testing and Certification

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).

### AQUADESIGN

#### **230/2330 IP44**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid and improved protection against accidental contact

#### **230/2335**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

#### **230/2330 IP44**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, labelling field and improved protection against accidental contact

#### **230/2330 IP44**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, lockable and improved protection against accidental contact

### Renova

#### **230/EAV54699**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

### Anti vandalism

#### **230/S1B7217902**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with improved protection against accidental contact

### OVE Testing and Certification

Accredited by the Federal Ministry for Digital and Economic Affairs as Certification Body for products within the scope as given in the official decree and published under [www.bmdw.gv.at/akkreditierung](http://www.bmdw.gv.at/akkreditierung).