

# AENOR

## AENOR Product Certificate Low Voltage Material



030/002253

AENOR certifies that the organization

### SCHNEIDER ELECTRIC ESPAÑA, S.A.

registered office	CL BAC DE RODA, 52 EDIFICIO A 08019 BARCELONA (España)
supplies	Circuit-Breakers
in compliance with	UNE-EN 60898-1:2004 (EN 60898-1:2003) UNE-EN 60898-1:2004/A11:2006 (EN 60898-1:2003/A11:2005) UNE-EN 60898-1:2004/A1:2005 (EN 60898-1:2003/A1:2004) UNE-EN 60898-1:2004/A12:2009 (EN 60898-1:2003/A12:2008) UNE-EN 60898-1:2004/A13:2013 (EN 60898-1:2003/A13:2012) UNE-EN 60947-2:2007 (EN 60947-2:2006) UNE-EN 60947-2:2007/A1:2011 (EN 60947-2:2006/A1:2009) UNE-EN 60947-2:2007/A2:2013 (EN 60947-2:2006/A2:2013)
References	Specified in Annex to the Certificate
Production site	1, RUE MAURICE RAVEL - Z.I. DE CROUPILLAC - BP 229 30319 ALES (Francia)
Certification scheme	In order to grant this Certificate, AENOR has tested the product and has verified the quality system implemented for its manufacture. AENOR performs these tasks periodically while the Certificate has not been cancelled, in accordance with Specific Rules RP 030.15.
	This certificate supersedes 030/002253, dated 2011-05-05
First issued on	2011-05-05
Modified on	2017-03-06
Validity date	2022-03-06

Avelino BRITO  
General Manager

Original Electrónico

# AENOR

## AENOR Product Certificate Low Voltage Material

030/002253

### Annex to Certificate

Trade mark: Schneider Electric

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated service short-circuit breaking capacity (Ics)
A9F74101	1P	230/400 V-	1 A	6000 A	C	50 kA	50 kA
A9F74102	1P	230/400 V-	2 A	6000 A	C	50 kA	50 kA
A9F74103	1P	230/400 V-	3 A	6000 A	C	50 kA	50 kA
A9F74104	1P	230/400 V-	4 A	6000 A	C	50 kA	50 kA
A9F74170	1P	230/400 V-	0,5 A	6000 A	C	50 kA	50 kA
A9F74201	2P	400 V-	1 A	6000 A	C	50 kA	50 kA
A9F74202	2P	400 V-	2 A	6000 A	C	50 kA	50 kA
A9F74203	2P	400 V-	3 A	6000 A	C	50 kA	50 kA
A9F74204	2P	400 V-	4 A	6000 A	C	50 kA	50 kA
A9F74270	2P	400 V-	0,5 A	6000 A	C	50 kA	50 kA
A9F74301	3P	400 V-	1 A	6000 A	C	50 kA	50 kA
A9F74302	3P	400 V-	2 A	6000 A	C	50 kA	50 kA
A9F74303	3P	400 V-	3 A	6000 A	C	50 kA	50 kA
A9F74304	3P	400 V-	4 A	6000 A	C	50 kA	50 kA
A9F74370	3P	400 V-	0,5 A	6000 A	C	50 kA	50 kA
A9F74401	4P	400 V-	1 A	6000 A	C	50 kA	50 kA
A9F74402	4P	400 V-	2 A	6000 A	C	50 kA	50 kA
A9F74403	4P	400 V-	3 A	6000 A	C	50 kA	50 kA
A9F74404	4P	400 V-	4 A	6000 A	C	50 kA	50 kA
A9F74470	4P	400 V-	0,5 A	6000 A	C	50 kA	50 kA
A9F74601	1P+N	230 V-	1 A	6000 A	C	50 kA	50 kA
A9F74602	1P+N	230 V-	2 A	6000 A	C	50 kA	50 kA
A9F74603	1P+N	230 V-	3 A	6000 A	C	50 kA	50 kA
A9F74604	1P+N	230 V-	4 A	6000 A	C	50 kA	50 kA
A9F79106	1P	230/400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79110	1P	230/400 V-	10 A	6000 A	C	10 kA	7,5 kA

First issued on 2011-05-05  
Modified on 2017-03-06  
Validity date 2022-03-06

Original Electrónico

AENOR INTERNACIONAL S.A.U.  
Génova, 6. 28004 Madrid. España  
Tel. 91 432 60 00.- www.aenor.com

# AENOR

## AENOR Product Certificate Low Voltage Material

030/002253

### Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F79116	1P	230/400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79120	1P	230/400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79125	1P	230/400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79132	1P	230/400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79140	1P	230/400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79150	1P	230/400 V-	50 A	6000 A	C	10 kA	7,5 kA
A9F79163	1P	230/400 V-	63 A	6000 A	C	10 kA	7,5 kA
A9F79206	2P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79210	2P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79216	2P	400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79220	2P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79225	2P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79232	2P	400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79240	2P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79250	2P	400 V-	50 A	6000 A	C	10 kA	7,5 kA
A9F79263	2P	400 V-	63 A	6000 A	C	10 kA	7,5 kA
A9F79306	3P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79310	3P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79316	3P	400 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79320	3P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79325	3P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79332	3P	400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79340	3P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79350	3P	400 V-	50 A	6000 A	C	10 kA	7,5 kA
A9F79363	3P	400 V-	63 A	6000 A	C	10 kA	7,5 kA
A9F79406	4P	400 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79410	4P	400 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79416	4P	400 V-	16 A	6000 A	C	10 kA	7,5 kA

First issued on 2011-05-05  
Modified on 2017-03-06  
Validity date 2022-03-06

Original Electrónico

AENOR INTERNACIONAL S.A.U.  
Génova, 6. 28004 Madrid. España  
Tel. 91 432 60 00.- www.aenor.com

# AENOR

## AENOR Product Certificate Low Voltage Material

030/002253

### Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F79420	4P	400 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79425	4P	400 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79432	4P	400 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79440	4P	400 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79450	4P	400 V-	50 A	6000 A	C	10 kA	7,5 kA
A9F79463	4P	400 V-	63 A	6000 A	C	10 kA	7,5 kA
A9F79606	1P+N	230 V-	6 A	6000 A	C	10 kA	7,5 kA
A9F79610	1P+N	230 V-	10 A	6000 A	C	10 kA	7,5 kA
A9F79616	1P+N	230 V-	16 A	6000 A	C	10 kA	7,5 kA
A9F79620	1P+N	230 V-	20 A	6000 A	C	10 kA	7,5 kA
A9F79625	1P+N	230 V-	25 A	6000 A	C	10 kA	7,5 kA
A9F79632	1P+N	230 V-	32 A	6000 A	C	10 kA	7,5 kA
A9F79640	1P+N	230 V-	40 A	6000 A	C	10 kA	7,5 kA
A9F79650	1P+N	230 V-	50 A	6000 A	C	10 kA	7,5 kA
A9F79663	1P+N	230 V-	63 A	6000 A	C	10 kA	7,5 kA
A9F84101	1P	230/400 V-	1 A	10000 A	C	70 kA	70 kA
A9F84102	1P	230/400 V-	2 A	10000 A	C	70 kA	70 kA
A9F84103	1P	230/400 V-	3 A	10000 A	C	70 kA	70 kA
A9F84104	1P	230/400 V-	4 A	10000 A	C	70 kA	70 kA
A9F84170	1P	230/400 V-	0,5 A	10000 A	C	70 kA	70 kA
A9F84201	2P	400 V-	1 A	10000 A	C	70 kA	70 kA
A9F84202	2P	400 V-	2 A	10000 A	C	70 kA	70 kA
A9F84203	2P	400 V-	3 A	10000 A	C	70 kA	70 kA
A9F84204	2P	400 V-	4 A	10000 A	C	70 kA	70 kA
A9F84270	2P	400 V-	0,5 A	10000 A	C	70 kA	70 kA
A9F84301	3P	400 V-	1 A	10000 A	C	70 kA	70 kA
A9F84302	3P	400 V-	2 A	10000 A	C	70 kA	70 kA
A9F84303	3P	400 V-	3 A	10000 A	C	70 kA	70 kA

First issued on 2011-05-05  
Modified on 2017-03-06  
Validity date 2022-03-06

Original Electrónico

AENOR INTERNACIONAL S.A.U.  
Génova, 6. 28004 Madrid. España  
Tel. 91 432 60 00.- www.aenor.com

# AENOR

## AENOR Product Certificate Low Voltage Material

030/002253

### Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F84304	3P	400 V-	4 A	10000 A	C	70 kA	70 kA
A9F84370	3P	400 V-	0,5 A	10000 A	C	70 kA	70 kA
A9F84401	4P	400 V-	1 A	10000 A	C	70 kA	70 kA
A9F84402	4P	400 V-	2 A	10000 A	C	70 kA	70 kA
A9F84403	4P	400 V-	3 A	10000 A	C	70 kA	70 kA
A9F84404	4P	400 V-	4 A	10000 A	C	70 kA	70 kA
A9F84470	4P	400 V-	0,5 A	10000 A	C	70 kA	70 kA
A9F89106	1P	230/400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89110	1P	230/400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89116	1P	230/400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89120	1P	230/400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89125	1P	230/400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89132	1P	230/400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89140	1P	230/400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89150	1P	230/400 V-	50 A	10000 A	C	15 kA	7,5 kA
A9F89163	1P	230/400 V-	63 A	10000 A	C	15 kA	7,5 kA
A9F89206	2P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89210	2P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89216	2P	400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89220	2P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89225	2P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89232	2P	400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89240	2P	400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89250	2P	400 V-	50 A	10000 A	C	15 kA	7,5 kA
A9F89263	2P	400 V-	63 A	10000 A	C	15 kA	7,5 kA
A9F89306	3P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89310	3P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89316	3P	400 V-	16 A	10000 A	C	15 kA	7,5 kA

First issued on 2011-05-05  
Modified on 2017-03-06  
Validity date 2022-03-06

Original Electrónico

AENOR INTERNACIONAL S.A.U.  
Génova, 6. 28004 Madrid. España  
Tel. 91 432 60 00.- www.aenor.com



# AENOR

## AENOR Product Certificate Low Voltage Material

030/002253

### Annex to Certificate

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Tripping current	Rated ultimate short-circuit breaking capacity (Icu)	Rated servicio short-circuit breaking capacity (Ics)
A9F89320	3P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89325	3P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89332	3P	400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89340	3P	400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89350	3P	400 V-	50 A	10000 A	C	15 kA	7,5 kA
A9F89363	3P	400 V-	63 A	10000 A	C	15 kA	7,5 kA
A9F89406	4P	400 V-	6 A	10000 A	C	15 kA	7,5 kA
A9F89410	4P	400 V-	10 A	10000 A	C	15 kA	7,5 kA
A9F89416	4P	400 V-	16 A	10000 A	C	15 kA	7,5 kA
A9F89420	4P	400 V-	20 A	10000 A	C	15 kA	7,5 kA
A9F89425	4P	400 V-	25 A	10000 A	C	15 kA	7,5 kA
A9F89432	4P	400 V-	32 A	10000 A	C	15 kA	7,5 kA
A9F89440	4P	400 V-	40 A	10000 A	C	15 kA	7,5 kA
A9F89450	4P	400 V-	50 A	10000 A	C	15 kA	7,5 kA
A9F89463	4P	400 V-	63 A	10000 A	C	15 kA	7,5 kA

First issued on 2011-05-05  
Modified on 2017-03-06  
Validity date 2022-03-06

Original Electrónico

AENOR INTERNACIONAL S.A.U.  
Génova, 6. 28004 Madrid. España  
Tel. 91 432 60 00.- www.aenor.com