



08 September 2016

33-37 Port Wakefield Road, Gepps Cross SA 5094, Australia

Schneider Electric (Australia) Pty. Ltd.

Attention: Les Blaszczyk

Dear Sir / Madam,

APPROVAL OF PRESCRIBED EQUIPMENT

Enclosed is the Certificate(s) in respect to your recent application received by Office of the Technical Regulator.

Please take time to check the certificate to ensure that all details are correct in accordance with your application, and that you understand all of the conditions imposed on the approval.

Should you have any queries, please contact George Nestic on telephone ,or email george.nestic@sa.gov.au

Any samples that accompanied your application are available for collection, and if not collected within 20 business days of the date hereon may be disposed of.

Notification must be given to Office of the Technical Regulator of any change of registered Address within 20 business days.

Yours faithfully

A handwritten signature in blue ink that reads "George Nestic".

AUTHORISED OFFICER

Ref: OTR160497/00



Certificate Number: OTR160497/00



Certificate of Approval

This is to certify that the Authorised officer has approved the electrical equipment described hereunder.

Registered Declarant: Schneider Electric (Australia) Pty. Ltd.
33-37 Port Wakefield Road, Gepps Cross SA 5094, Australia

Required Marking: OTR160497

Electrical equipment covered by this approval must comply in all respects with the approved article, and prior to being supplied or offered for supply, must be clearly and indelibly marked with the required marking indicated above, or the Regulatory Compliance Mark (RCM) provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled.

Any modifications to the electrical equipment or its place of manufacture must be approved by Office of the Technical Regulator prior to the equipment being supplied or offered for supply.

Notification must be given to Office of the Technical Regulator of any change to the name or address of the holder of the certificate within 20 business days.

ARTICLE DETAILS

Electrical Equipment:	Level 3 Residual Current Device Residual current operated circuit-breakers with integral overcurrent protection (RCBO)
Relevant Standards:	AS/NZS 61009.1:2015
Expiry Date:	08 September 2021
Conditions of Approval:	

A handwritten signature in blue ink, appearing to read "George Nasic".

DATE OF APPROVAL: 08 September 2016 Page: (2 / 7)

Authorised officer



Government of South Australia
Department of State Development

Certificate Number: OTR160497/00



Approval details

--

Model	4RCBM210/30, 4RCBM216/30, 4RCBM220/30, 4RCBM225/30, 4RCBM232/30, 4RCBM240/30
Rated at	Input: 230-240 Vac, 10, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal
Comments	4RCBM series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type AC, 10 kA (for 10, 16 & 20 A RCBO), 6 kA (for 25, 32 & 40 A RCBO), overcurrent protection with C type tripping curve.

Model	4RCBM210SI30, 4RCBM216SI30, 4RCBM220SI30, 4RCBM225SI30, 4RCBM232SI30, 4RCBM240SI30
Rated at	Input: 230-240 Vac, 10, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal
Comments	4RCBMSI series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type A, SI - resistant to 3000 A surge, 10 kA (for 10, 16 & 20 A RCBO), 6 kA (for 25, 32 & 40 A RCBO), overcurrent protection with C type tripping curve.

Model	RCBM206/30, RCBM210/30, RCBM216/30, RCBM220/30,
-------	---

A handwritten signature in blue ink that reads 'George Nasic'.



Certificate Number: OTR160497/00



	RCBM225/30, RCBM232/30
Rated at	Input: 230-240 Vac, 6, 10, 16, 20, 25 & 32 A, 50 Hz
Trade Name	Clipsal
Comments	RCBM series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type AC, 6 kA, overcurrent protection with C type tripping curve.

Model	P4B6AC30/6000, P4B10AC30/6000, P4B13AC30/6000, P4B16AC30/6000, P4B20AC30/6000, P4B25AC30/6000, P4B32AC30/6000, P4B40AC30/6000
Rated at	Input: 230-240 Vac, 6, 10, 13, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-6000A series or Clipsal P4-RCBM-6000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type AC, 6 kA, overcurrent protection with B type tripping curve.

Model	P4B40A30/6000, P4B10A30/6000, P4B13A30/6000, P4B16A30/6000, P4B20A30/6000, P4B25A30/6000, P4B32A30/6000, P4B6A30/6000
Rated at	Input: 230-240 Vac, 6, 10, 13, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-6000A series or Clipsal P4-RCBM-6000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type A, 6 kA, overcurrent protection with B type tripping curve.

George Nasic



Certificate Number: OTR160497/00



Model	P4C10AC30/6000, P4C13AC30/6000, P4C16AC30/6000, P4C20AC30/6000, P4C25AC30/6000, P4C32AC30/6000, P4C40AC30/6000, P4C6AC30/6000
Rated at	Input: 230-240 Vac, 6, 10, 13, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-6000A series or Clipsal P4-RCBM-6000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type AC, 6 kA, overcurrent protection with C type tripping curve.

Model	P4C10A30/6000, P4C13A30/6000, P4C16A30/6000, P4C20A30/6000, P4C25A30/6000, P4C32A30/6000, P4C40A30/6000, P4C6A30/6000
Rated at	Input: 230-240 Vac, 6, 10, 13, 16, 20, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-6000A series or Clipsal P4-RCBM-6000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type A, 6 kA, overcurrent protection with C type tripping curve.

Model	P4C25Asi30/6000, P4C32Asi30/6000, P4C40Asi30/6000
Rated at	Input: 230-240 Vac, 25, 32 & 40 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-6000A series or Clipsal

George Nasic



Certificate Number: OTR160497/00



	P4-RCBMSI-6000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type A, SI - resistant to 3000 A surge, 6 kA, overcurrent protection with C type tripping curve.
--	--

Model	P4C10AC30/10000, P4C16AC30/10000, P4C20AC30/10000
Rated at	Input: 230-240 Vac, 10, 16 & 20 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-10000A series or Clipsal P4-RCBM-10000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type AC, 10 kA, overcurrent protection with C type tripping curve.

Model	P4C10Asi30/10000, P4C16Asi30/10000, P4C20Asi30/10000
Rated at	Input: 230-240 Vac, 10, 16 & 20 A, 50 Hz
Trade Name	Clipsal or Schneider
Comments	Schneider P4-10000A series or Clipsal P4-RCBMSI-10000A series, 1P+N (with a switched neutral pole), two modules wide, 30 mA, Type A, SI - resistant to 3000 A surge, 10 kA, overcurrent protection with C type tripping curve.



Certificate Number: OTR160497/00



A handwritten signature in blue ink that reads "George Nasic".

DATE OF APPROVAL: 08 September 2016 Page: (7 / 7)

Authorised officer



Government of South Australia
Department of State Development