



IEC 61850 Certificate Level A¹

No. 74100113-MOC/INC 11-1518

Issued to:
Schneider Electric
2195 Keating Cross Road
Saanichton, BC
Canada V8M 2A5

For the product:
ION8650 meter
Firmware version v400



The product has not shown to be non-conforming to:
IEC 61850-6, 7-1, 7-2, 7-3, 7-4 and 8-1
Communication networks and systems in substations

The conformance test has been performed according to IEC 61850-10 with product's protocol, model and technical issue implementation conformance statements: "IEC 61850 and ION Technology, 70022-0125" also including product's extra information for testing.

The following IEC 61850 conformance blocks have been tested with a positive result (number of relevant and executed test cases / total number of test cases as defined in the UCA International Users Group Device Test procedures v2.2b):

1 Basic Exchange (15/24)	12a Direct Control (4/11)
2 Data Sets (3/6)	13 Time Synchronization (3/5)
5 Unbuffered Reporting (13/18)	
6 Buffered Reporting (15/20)	

This Certificate includes a summary of the test results as carried out at KEMA in the Netherlands with UniCAsim 61850 version 3.23.02 with test suite 3.21.03 and UniCA 61850 analyzer 4.23.02. The test is based on the UCA International Users Group Device Test Procedures version 2.2b. This document has been issued for information purposes only, and the original paper copy of the KEMA report: No. 74100113-MOC/INC 11-1517 will prevail.

The test has been carried out on one single specimen of the products as referred above and submitted to KEMA by Schneider Electric. The manufacturer's production process has not been assessed. This Certificate does not imply that KEMA has certified or approved any product other than the specimen tested.

Arnhem, 10 June 2011


M. Adriaerisen
Regional Director Management & Operations Consulting


Richard Schimmel
Certification Manager

1 Level A - Independent Test lab with certified ISO 9000 or ISO 17025 Quality System

Copyright © KEMA Nederland B.V., Arnhem, the Netherlands. All rights reserved. Please note that any electronic version of this KEMA certificate is provided to KEMA's customer for convenience purposes only. It is prohibited to update or change it in any manner whatsoever, including but not limited to dividing it into parts. In case of a conflict between the electronic version and the original version, the original paper version issued by KEMA will prevail.



Applicable Test Procedures from the UCA International Users Group Device Test Procedures version 2.2b

Conformance Block	Mandatory	Conditional
1: Basic Exchange	Ass1, Ass2, Ass3, AssN2, AssN3, AssN4, AssN5 Srv1, Srv2, Srv3, Srv4, Srv5, SrvN1abcd, SrvN4	Srv8
2: Data Sets	Dset1, Dset10a, DsetN1ae	
5: Unbuffered Reporting	Rp1, Rp2, Rp3, Rp4, Rp7, Rp10 RpN1, RpN2, RpN3, RpN4	Rp5, Rp9, RpN5
6: Buffered Reporting	Br1, Br2, Br3, Br4, Br7, Br8, Br9, Br12 BrN1, BrN2, BrN3, BrN4, BrN5	Br5, Br11
12a: Direct control	CltN3, CtlN8 DOns1, DOns3	
13: Time sync	Tm1, Tm2, TmN1	