

SGS

LICENCE

No. 17393 replaces No.14578

Issued to:
Applicant:
Schneider Electric Industries SAS
35 Rue Joseph Monier
F-92506 RUEIL-MALMAISON CEDEX
France



Licensee:
Schneider Electric Industries SAS
35 Rue Joseph Monier
F-92506 RUEIL-MALMAISON CEDEX
France



Product : push-button switches (for fixed installations)
Trade name(s) : SCHNEIDER ELECTRIC
Type(s)/model(s) : Series MUREVA (see appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 1463

SGS CEBEC hereby grants the right to use the CEBEC certification mark

The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.


This licence is issued on: 13/09/2011

Ir. C. Lana,
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



005-PROD



SGS Belgium NV-Division SGS CEBEC
Business Riverside Park
Bld Internationalelaan 55 Bld. D
B-1070 Brussels
Tel.+32(0)2 556 00 20 Fax.+32(0)2 556 00 36

This certificate is issued by the company under its General Conditions for Certification Services accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitations of liability defined therein and in the Test Report herein mentioned which findings are reflected in this Certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	:	push-button switches (for fixed installations)
Trade name(s)	:	SCHNEIDER ELECTRIC
Type(s)/Model(s)	:	Series MUREVA (see appendix)
rated current (In)	:	10 A
rated voltage (Un)	:	250 Vac
method of application	:	surface type
method of installation	:	A
resistance to impact (IK)	:	IK 07 or IK 08
degree of protection	:	IP 55
pattern no(s).	:	1 and 2x1
type of terminals	:	screw-type
contact opening (gap)	:	normal
certification mark	:	complies with the requirements
markings	:	are shown on the body

Additional information

See Appendix

TESTS**Test requirements**

NBN EN 60669-1 based on EN 60669-1:1999 + A1:2002 + A2:2008

Test results

The test results are laid down in certification file ref.591953/01



Remarks

This certificate is based on certificate ref. CCA-FR 609966 and test report(s) ref. 60040461-540518 & 105653-609968


Conclusion

The examination proved that all test requirements were met.

Checked by, project leader : Zanutto Luigi - 13/09/2011

Department Manager,
Product Certification :

Certification Manager :

 2011-09-13



FACTORY LOCATION(S)

Sarel Appareillages Electriques
52, route de Phalsbourg
PO Box 106
67 269 SARRE-UNION Cédex
France

SERIES MUREVA : Push-Button Switches

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN35026	1	26	Surface type	Grey/Grey	No/No	IK07	Single grey Ref. ENN37911	1 Large
ENN39026	1	26	Surface type	White/White	No/No	IK07	Single white Ref. ENN39911	1 Large
ENN35126	1	26	Surface type	Grey/Blue	No/No	IK08	Single grey Ref. ENN37911	1 Large
ENN35042	2x1	25	Surface type	Grey/Grey	Yes/No	IK07	Single grey Ref. ENN37911	2 Narrow
ENN39042	2x1	25	Surface type	White/white	Yes/No	IK07	Single white Ref. ENN39911	2 Narrow
ENN35043	2x1	25	Surface type	Grey/Grey	Yes/No	IK07	Single grey Ref. ENN37911	2 Narrow
ENN39043	2x1	25	Surface type	White/White	Yes/No	IK07	Single white Ref. ENN39911	2 Narrow
ENN35626	1	26	Surface type GSB	Grey/Grey	No/No	IK07	Single grey Ref. ENN37911	1 Large

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN39626	1	26	Surface type GSB	White/White	No/No	IK07	Single white Ref.ENN39911	1 Large
ENN37026	1	26	Surface type composable	Grey/Grey	No/No	IK07	Supplied separately*	1 Large
ENN39726	1	26	Surface type composable	White/White	No/No	IK07	Supplied separately*	1 Large
ENN35030	1	26	Surface type	Grey/Grey	No/No	IK07	Single grey Ref.ENN37911	1 Large + Bell mark
ENN39002	1	26	Surface type	White/White	No/No	IK07	Single white Ref.E NN39911	1 Large + Bell mark
ENN37031	1	26	Surface type composable	Grey/Grey	No/No	IK07	Supplied separately*	1 Large + Bell mark
ENN39731	1	26	Surface type composable	White/White	No/No	IK07	Supplied separately*	1 Large + Bell mark
ENN37762	1	26	Surface type composable, deconditioning	Grey/Grey	No/No	IK07	Supplied separately*	1 Large + Bell mark

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN37962	1	26	Surface type composable, deconditioning	White/White	No/No	IK07	Supplied separately*	1 Large + Bell mark
ENN35032	1	26	Surface type	Grey/Grey	No/No	IK07	Single grey Ref.ENN37911	1 Large + Lamp mark
ENN39003	1	26	Surface type	White/White	No/No	IK07	Single whiteRef.E NN39911	1 Large + Lamp mark
ENN37033	1	26	Surface type composable	Grey/Grey	No/No	IK07	Supplied separately*	1 Large + Lamp mark
ENN39733	1	26	Surface type composable	White/White	No/No	IK07	Supplied separately*	1 Large + Lamp mark
ENN37764	1	26	Surface type composable deconditioning	Grey/Grey	No/No	IK07	Supplied separately*	1 Large + Lamp mark
ENN37964	1	26	Surface type composable deconditioning	White/White	No/No	IK07	Supplied separately*	1 Large + Lamp mark
ENN35028	1	26	Surface type	Grey/Grey	No/Yes	IK07	Single grey Ref.ENN37911	1 Large +light window

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN39028	1	26	Surface type	White/White	No/Yes	IK07	Single white Ref. ENN39911	1 Large +light window
ENN35128	1	26	Surface type	Grey/Grey	No/Yes	IK08	Single grey Ref. ENN37911	1 Large +light window
ENN35628	1	26	Surface type GSB	Grey/Grey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large +light window
ENN39628	1	26	Surface type GSB	White/white	No/Yes	IK07	Single white Ref. ENN39911	1 Large +light window
ENN37028	1	26	Surface type composable	Grey/Grey	No/Yes	IK07	Supplied separately*	1 Large +light window
ENN39728	1	26	Surface type composable	White/white	No/Yes	IK07	Supplied separately*	1 Large +light window
ENN35000	1	26	Surface type	Grey/Grey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large +light window + bell mark

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN39000	1	26	Surface type	White/white	No/Yes	IK07	Single white Ref. ENN39911	1 Large +light window + bell mark
ENN35001	1	26	Surface type	Grey/Grey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large +light window + lamp mark
ENN39001	1	26	Surface type	White/white	No/Yes	IK07	Single white Ref. ENN39911	1 Large +light window + lamp mark
ENN35029	1	26	Surface type	Grey/Grey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large + label holder
ENN39029	1	26	Surface type	White/White	No/Yes	IK07	Single white Ref. ENN39911	1 Large + label holder
ENN35629	1	26	Surface type GSB	GreyGrey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large + label holder
ENN39629	1	26	Surface type GSB	White/White	No/Yes	IK07	Single white Ref. ENN39911	1 Large + label holder

Product reference	Pattern Nbr.	Base type	Method of application	Housing /Rocker colour	Rolling shutter / Pilot light	Impact resistance	Box	Actuator member
ENN35029	1	26	Surface type	Grey/Grey	No/Yes	IK07	Single grey Ref. ENN37911	1 Large + label holder + bell mark
ENN35326	2x1	25	Surface type	Grey/Grey	Yes/No	IK07	Single grey Ref. ENN37911	2 Narrow
ENN35228	2x1	25	Surface type	Grey/Grey	Yes/No	IK07	Single grey Ref. ENN37911	2 Narrow
ENN39228	2x1	25	Surface type	White/White	Yes/No	IK07	Single white Ref. ENN39911	2 Narrow

* Possible boxes.

Boxe reference	Description	Colour
ENN37911	Single box	Grey
ENN39911	Single box	White
ENN37912	Double vertical box	Grey
ENN39912	Double vertical box	White
ENN37914	Double horizontal box	Grey
ENN39914	Double horizontal box	White
ENN37913	Triple horizontal box	Grey
ENN39913	Triple horizontal box	White