

# Certificate




for European Product Safety

Reference No. 1918694


## Electronic control units for luminaires

<i>Type designation</i>	SBD 1-10V
<i>Certificate holder</i>	<b>Schneider Electric Industries SAS</b> 35 rue Joseph Monier 92500 Rueil-Malmaison FRANCE
<i>The product complies with the standard(s)</i>	EN 60669-1:1999 and A1+A2 EN 60669-2-1:2004+A1+A12
<i>Date of expiry</i>	13 January 2025
<i>EU Directive information</i>	According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

Additional information in Appendix.

<i>Certification Body</i>	Intertek Semko AB, Product Certification	<i>Place</i>	Kista - Stockholm
<i>Signed</i>	 Henrik Wikström	<i>Date</i>	13 January 2020 Page 1 of 3

This certificate is issued in accordance with the terms and conditions set out in the Appendix.



## Intertek Appendix

Reference No. 1918694

### Technical data

Type designation	SBD 1-10V
Rated voltage (V)	230V AC
Rated power (W)	400W incandescent lamps 400VA electronic step-down converter for low-voltage halogen lamps
Frequency (Hz)	50Hz
IP-Class	IP20, IP44 when using specific Exxact designs
Pattern No.	1
Type of terminals	Pillar, screw type
Trade mark:	<b>Schneider</b> Electric

### Product information

Electronic dimmer for electronic ballasts and transformers, flush mounting, fuse F6,3AH and  $\mu$ -disconnection

Cover designs for inserts SBD 1-10V. If the design includes frames sold separately the material is listed in column 3. All frames are from 1-5 gang.

Design	Reference Cover	Reference Frame
Trend	100949	100520
Trend Solid	100949	101543 (thermoplastic/glass/metallic)
Renova/Arezzo	101368	101370
Artic	13620	13601 (thermoplastic)
Artic Decor	13620	13806 (thermoplastic/glass/metallic)
Senso	20005157	20005048/20005050
Fashion	227010-0-1	21169.51-0:1
Riva	227010-0-1	204120-0-1
Scala	227010-0-1	21169.70-0:1
Novia	100634	100600 + 100601
Classic	227010-0-1	21169.151-0:1
Joy	267010-0-1	264100-0-1
MPLAN (System M)	5699	4861 (thermoplastic)
MPLAN II (System M)	5699	4881 (thermoplastic)
MPLAN metal (System M)	5699	4751 (metallic)
M-PLAN real glass (System M)	5699	4891 (real glass)
M-ARC (System M)	5699	4851 (thermoplastic)
M-STAR (System M)	5699	4871 (metallic)
Atelier-M (System M)	5699	3881 (thermoplastic)

This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.



## Intertek Appendix

Reference No. 1918694

1-M (System M)	5699	3891 (thermoplastic)
M-Smart (System M)	5699	4841 (thermoplastic/thermoset)
Elegance (System M)	5699	4021 (thermoplastic), 4031 (metallic), 4041 (glass), 4051 (wood)
ARTEC	5720	4811 (thermoplastic/metallic/thermoset)
Antik	5720	4831 (thermoplastic/metallic)
D-Life	NHA5193102	NHA2920502 (thermoplastic), NHA2923102 (metal), NHA2922102 (glass/stone)
Forum	13620	W450104
Duet	-	-
Wessen 59	-	-
Exxact Primo	BBV39712	BBV49557 (gasket), BBV49583 (Primo IP44)
Exxact Basic	BBV39712	BBV49557 (gasket), BBV49550 (Basic IP44)
Exxact	BBV39712	Combi BBV49575; Basic BBV49550, Primo BBV49558; Solid BBV49558, Solid Glass S1A45091, Primo BBV49583 (IP2x)
Delo (Odace)	BBV4007302	BBV4007602 + S1A2148202
Unica	2004912	6.002.—

**Manufacturing site(s)** Enics Eesti AS  
Valga mnt. 7 A  
61504 Elva  
ESTONIA

According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

This certificate replaces previously issued ref. No. 1022665 dated 18 January 2011. A new certificate has been issued on account of renewal of certificate.

This certificate is based on CB with ref. No. DE1-61768 dated 2019-03-14, issued by VDE.

**Certification Body** Intertek Semko AB, Product Certification **Place** Kista - Stockholm

**Signed**

Henrik Wikström

**Date** 13 January 2020

*This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.*