

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Circuit-breakers for overcurrent protection for household and similar installations

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens
F-38050 Grenoble Cedex 9
France

Name and address of the manufacturer

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens
F-38050 Grenoble Cedex 9
France

Name and address of the factory

Note: When more than one factory, please report on page 2

SCHNEIDER ELECTRIC THAILAND CO., LTD.
540 Soi 9 Bangpoo Industrial estate,
Sukhmit Road, Muang District
10280 Samutprakarn
Thailand

[Additional information on page 2](#)

Ratings and principal characteristics

1P, 1P+N, 2P, 3P or 4P;
Ue = 230/400 V (1P), 230 V (1P+N) or 400 V (2P, 3P and 4P);
50-60 Hz; Icn = 6000 A
Curve C – In = 6, 10, 13, 16, 20, 25 or 32 A
(see also pages 6 and 7 of Test Report No. PB22-0080370-01-00
and/or Additional Sheet)

Trademark / Brand (if any)



Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

iK60N series
(see also page 7 of Test Report No. PB22-0080370-01-00 or Additional Sheet)

Additional information (if necessary may also be reported on page 2)

-
 [Additional information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60898-1:2015, IEC 60898-1:2015/AMD1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

PB22-0080370-01-00 and from PB22-0080370-01-01 to PB22-0080370-01-19

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-20138 Milano
Italy



Date: 2023-02-03

Signature: Mauro Casari

IEC

IECEE



Ref. Certif. No.

IT-23508

Additional factory

SCHNEIDER ELECTRIC BULGARIA EOOD
Plovdiv plant
4202 Radinovo
Bulgaria

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-20138 Milano
Italy



Date: 2023-02-03

Signature: Mauro Casari

**Generic reference of the circuit-breakers for
overcurrent protection iK60N series and related ratings**

Generic reference	Number of poles	Rated voltage	Curve	Rated current
iK60N 1P 6A C	1P	230/400 V	C	6 A
iK60N 1P 10A C	1P	230/400 V	C	10 A
iK60N 1P 13A C	1P	230/400 V	C	13 A
iK60N 1P 16A C	1P	230/400 V	C	16 A
iK60N 1P 20A C	1P	230/400 V	C	20 A
iK60N 1P 25A C	1P	230/400 V	C	25 A
iK60N 1P 32A C	1P	230/400 V	C	32 A
iK60N 1P+N 6A C	1P+N	230 V	C	6 A
iK60N 1P+N 10A C	1P+N	230 V	C	10 A
iK60N 1P+N 13A C	1P+N	230 V	C	13 A
iK60N 1P+N 16A C	1P+N	230 V	C	16 A
iK60N 1P+N 20A C	1P+N	230 V	C	20 A
iK60N 1P+N 25A C	1P+N	230 V	C	25 A
iK60N 1P+N 32A C	1P+N	230 V	C	32 A
iK60N 2P 6A C	2P	400 V	C	6 A
iK60N 2P 10A C	2P	400 V	C	10 A
iK60N 2P 13A C	2P	400 V	C	13 A
iK60N 2P 16A C	2P	400 V	C	16 A
iK60N 2P 20A C	2P	400 V	C	20 A
iK60N 2P 25A C	2P	400 V	C	25 A
iK60N 2P 32A C	2P	400 V	C	32 A
iK60N 3P 6A C	3P	400 V	C	6 A
iK60N 3P 10A C	3P	400 V	C	10 A
iK60N 3P 13A C	3P	400 V	C	13 A
iK60N 3P 16A C	3P	400 V	C	16 A
iK60N 3P 20A C	3P	400 V	C	20 A
iK60N 3P 25A C	3P	400 V	C	25 A
iK60N 3P 32A C	3P	400 V	C	32 A
iK60N 4P 6A C	4P	400 V	C	6 A
iK60N 4P 10A C	4P	400 V	C	10 A
iK60N 4P 13A C	4P	400 V	C	13 A
iK60N 4P 16A C	4P	400 V	C	16 A
iK60N 4P 20A C	4P	400 V	C	20 A
iK60N 4P 25A C	4P	400 V	C	25 A
iK60N 4P 32A C	4P	400 V	C	32 A