




Ref. Certif. No.  
**SE-87661**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**


**CB TEST CERTIFICATE**

Product	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBO's)
Name and address of the applicant	Schneider Shanghai Low Voltage Terminal Apparatus Co., Ltd. 1319 Pingan Rd., Minhang Zone, Shanghai, P.R. CHINA
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Same as applicant
Ratings and principal characteristics	See page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	iSPN Vigi, iDif K, A $\Delta$ 63 K
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 61009-1:2010+A1+A2 IEC 61009-2-2:1991
As shown in the Test Report Ref. No. which forms part of this Certificate	170300490SHA-001

This CB Test Certificate is issued by the National Certification Body

**Intertek Semko AB**  
Box 1103  
SE-164 22 Kista, Sweden  
Int +46 8 750 00 00  
  
Date: 14 July 2017



Signature:   
Leif Söderlund

**Ratings and principal characteristics**

Model(s)	Ue(V)	Icn(A)	I $\Delta$ n(mA)	Type	In(A) and Type
iSPN Vigi	240V	6000	10, 30	A, AC	C6, C10, C16, C20, C25, C32
iSPN Vigi	110V	6000	30	A, AC	C6, C10, C16, C20, C25, C32
iDif K	230V	6000	30	A, AC	C6, C10, C16, C20, C25, C32
AД63 K	230V	4500	30	A, AC	C6, C10, C16, C20, C25, C32

**Additional information (if necessary)**

IEC 61009-1:2010 (Third Edition) +A1:2012 +A2:2013 used in conjunction with IEC 61009-2-2:1991 (First Edition).

Covered also AS/NZS 61009.1 – 2015 and BS EN 61009-1:2012 +A1:2014 +A2:2014 +A11:2015 +A12: 2016.

Date: 14 July 2017

Signature: *Leif Söderlund*