

IEC**IECEE**

®

TM

Ref. Certif. No.

CN53062

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Control and signaling units

Name and address of the applicant

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the manufacturer

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

PT. Schneider Electric Manufacturing Batam
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A
BIP Muka Kuning Kel.Muka Kuning Kec. Sungai Beduk –
Batam, Indonesia

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

XB7EA, XB7EH, XB7EL, XB7ES, XB7EV, XB7NS, XB7NT,
XB7NA, XB7NL, XB7NH, XB7NW, XB7NJ, XB7ND,
XB7NG

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-5-1:2016(4th Edition)

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2020CQC-094594

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Mar.24,2021

Signature:

Lu Mei

CB 0061145

XB7EA, XB7EH, XB7EL, XB7ES, XB7EV, XB7NS, XB7NT,
XB7NA, XB7NL, XB7NH, XB7NW, XB7NJ, XB7ND, XB7NG
XB7E:

Uimp:4kV;

Ui:250V;

Ith:2A;

Ue/Ie:AC-14: AC240V/0.3A, 120V/0.6A;

Indicator light:

Ue: Incandescent lamp:250V,50-60Hz;

Power supply by resistor:AC230V,50-60Hz;

LED:AC120V,50-60Hz, AC230V,50-60Hz,AC/DC 24V;

Degree of protection (IP code):IP54(front),IP20(back);

Mounting aperture:Φ22.0mm

XB7NS/NT:

Ui:250V;Uimp:6kV;

AC-15:Ue/Ie:AC240V/0.75A,AC120V/1.5A;

Ith:5A;

Degree of protection (IP code):IP65(Before installing the panel),IP20(After installing the panel);

Mounting aperture:Φ22.0mm

XB7NA, XB7NL, XB7NH, XB7NW, XB7NJ, XB7ND, XB7NG:

Uimp:4kV;

Ui:250V;

Ith:2A;

Ue/Ie:AC-14: AC240V/0.3A,AC120V/0.6A;

Degree of protection (IP code):IP65;

Mounting aperture:Φ22.5mm

Button with lamp:

Incandescent lamp:AC250Vmax,50/60Hz;

LED:AC230V,50/60Hz,AC120V,50/60Hz; AC/DC 24V

Page 1 of 1

Additional information (if necessary)

Date: Mar.24,2021

Signature: 

Lu Mei