



Certificate of Compliance

Certificate: 1156134

Master Contract: 240515

Project: 70130401

Date Issued: 2017-05-05

Issued to: Telemecanique/Schneider Electric Industries SAS
Zone Industrielle No. 3
L'Isle d'Espagnac, 16340
FRANCE

The products listed below are eligible to bear the CSA Mark shown



Issued by: *Khalil Ouldchama*
Khalil Ouldchama, P. Eng.

PRODUCTS

CLASS - C241102 - ELEVATOR EQUIPMENT-Enclosed Elevator-and Escalator Electrical Equipment

CLASS - C321103 - INDUSTRIAL CONTROL EQUIPMENT-Motor Controllers - Auxiliary Devices

Part A (Class 3211-03)

Limit Switches, Types XCK-L, ZCK-L, XCK-M, ZCK-M, XCK-ML and XCK-MR, code rating: A300 and/or Q300 when provided with contact blocks Types XEN-P, XE2N-P, XES-P, XE2S-P; B300 or R300 when provided with contact blocks Types XE3S-P, XE3N-P, same polarity or opposite polarity. Enclosure Type 4.

Note: The type designation may be completed with numbers and letters, indicating contact shape and mechanical details.

Part B (Class 3211-03)

Limit Switches, Cat Nos. XCK-S, XCK-SD, ZCK-S and ZCK-SD, followed by 1, 2, 3, 4, 5, 6, 7, 8 or 9, followed by a two digit number, may be followed by H7 or H29, may be followed by optional suffix, code rating: A300, Q300 when provided with contact blocks Types XEN-P, XE2N-P, XES-P, XE2S-P; B300 or R300 when provided with contact blocks Types XE3S-P, XE3N-P. Enclosure Types 4 and 12.



Certificate: 1156134
Project: 70130401

Master Contract: 240515
Date Issued: 2017-05-05

Note: The switches without NPT conduit entry may be marked with special purpose enclosure rating when provided with instructions in package indicating the kit of NPT-Metric adaptors necessary to maintain the effectiveness of the special purpose rating and the NPT conduit entry.

Part C (Class 3211-03)

Limit Switches, Types XCK-T and XCK-B, followed by 1, 5, 6, 7, 8 or 9, followed by 01, 02, 06, 10, 11, 18, 19, 21, 27, 28, 39, 45, 46, 54 or 55, may be followed by H7, H29 or H44, code rating:

A300 and/or Q300 same polarity or opposite polarity.

Enclosure Types 4X indoor and 12.

Notes:

1. The switches without NPT conduit entry may be marked with special purpose enclosure rating when provided with instructions in package indicating the kit of NPT-Metric adaptors necessary to maintain the effectiveness of the special purpose rating and the NPT conduit entry.
2. The limit switch Types XCK-B and XCK-T has been accepted as end of the line device, where only one conduit is used.

Part D (Class 2411-02, Class 3211-03)

Limit Switches, Types XCK-P, followed by 1, 5, 6, 7, 8 or 9, followed by 01, 02, 06, 10, 11, 18, 19, 21, 27, 28, 39, 45, 46, 54 or 55, may be followed by H7, H29 or H44, code rating:

A300 and/or Q300 same polarity or opposite polarity.

Enclosure Types 4X indoor and 12.

Notes:

1. The switches without NPT conduit entry may be marked with special purpose enclosure rating when provided with instructions in package indicating the kit of NPT-Metric adaptors necessary to maintain the effectiveness of the special purpose rating and the NPT conduit entry.
2. Limit switches Types XCK-P are “positive mechanical action”, except for Models XCK-P.06, -P.39 and – P.55.

APPLICABLE REQUIREMENTS

CSA-C22.2 No. 14-13	-	Industrial Control Equipment
CAN/CSA-C22.2 No. 94-M91	-	Special Purpose Enclosures
CAN/CSA-B44.1-14 / ASME-A17.5-2014	-	Elevator and Escalator Electrical Equipment