

AENOR

AENOR Product Certificate Low Voltage Material



030/002370

AENOR certifies that the organization

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office 35, RUE JOSEPH MONIER 92506 RUEIL MALMAISON CEDEX (Francia)

supplies Residual current operated circuit-breaker without integral overcurrent protection (RCCB's)

in compliance with UNE-EN 61008-1:2013 (EN 61008-1:2012)
UNE-EN 61008-1:2013/A1:2015 (EN 61008-1:2012/A1:2014)
UNE-EN 61008-1:2013/A2:2015 (EN 61008-1:2012/A2:2014)
UNE-EN 61008-2-1/A11:1999 (EN 61008-2-1:1994/A11:1998)
UNE-EN 61008-2-1:1996 (EN 61008-2-1:1994)

Trade mark Schneider Electric

See annex for more information.

Production site CM BARRANQUET, 57 46133 MELIANA (Valencia - España)

Certification scheme In order to grant this Certificate, AENOR has tested the product and has verified the quality system implemented for its manufacture. AENOR performs these tasks periodically while the Certificate has not been cancelled, in accordance with Specific Rules RP 030.15.

This certificate supersedes 030/002370, dated 2014-09-19

First issued on 2014-09-19
Modified on 2017-10-05
Validity date 2019-09-19

Rafael GARCÍA MEIRO
Chief Executive Officer

Original Electrónico

AENOR

AENOR Product Certificate Low Voltage Material

030/002370

Annex to Certificate

Trade mark Schneider Electric

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I m	I n c)	I Δ c	Type	Additional information
R9R11225	2P	25 A	230/240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(5)
R9R11240	2P	40 A	230/240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(4)
R9R11263	2P	63 A	230/240 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)/(3)
R9R11425	4P	25 A	400/415 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(5)
R9R11440	4P	40 A	400/415 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(4)
R9R11463	4P	63 A	400/415 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)/(3)
R9R14225	2P	25 A	230/240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(5)
R9R14240	2P	40 A	230/240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(4)
R9R14263	2P	63 A	230/240 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)/(3)
R9R14425	4P	25 A	400/415 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(5)
R9R14440	4P	40 A	400/415 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(1)/(4)
R9R14463	4P	63 A	400/415 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)/(3)
R9R15263	2P	63 A	230/240 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	ACS	(2)/(3)
R9R15463	4P	63 A	400/415 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	ACS	(2)/(3)

- (1) *First Family: Mobile Contact:(AgSnO₂)-- Mobile Contact Arm(Copper).Fixed Contact(AgC). Fixed Contact Arm(Copper). Output Terminal current carrying Part(Copper).*
- (2) *Second Family: Mobile Contact:(AgSnO₂)- Mobile Contact Arm(Copper). Fixed Contact: (AgC). - Fixed Contact Arm(Copper). Output Terminal current carrying Part(Silver coated Copper).*
- (3) *-5/40 °C. Shall be back up protected by gG 100 A fuse.*
- (4) *-5/40 °C. Shall be back up protected by gG 63 A fuse.*
- (5) *-5/40 °C. Shall be back up protected by gG 50 A Fuse*

First issued on 2014-09-19
Modified on 2017-10-05
Validity date 2019-09-19