

IEC**IECEE**

®

™

Ref. Certif. No.

CN53302

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Moulded Case Circuit-breakers

Name and address of the applicant

Schneider Electric (China) Co., Ltd.
Block A, No.6 East Wangjing Road, Chaoyang District, Beijing,
P.R.China

Name and address of the manufacturer

Fuji Electric Dalian Co., Ltd.
No.3 3rd Dongbei Street, Dalian Economic & Technical
Development Zone, Dalian, Liaoning Province, P.R.China

Name and address of the factory

Fuji Electric Dalian Co., Ltd.
No.3 3rd Dongbei Street, Dalian Economic & Technical
Development Zone, Dalian, Liaoning Province, P.R.China

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

EasyPact EZC250F/N/H

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016(5th Edition); IEC
60947-2:2016/AMD1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2020CQC-091616

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Apr.22,2021

Signature:

Lu Mei

CB 0061827

EasyPact EZC250F/N/H

Uimp:6kV;

Ui:690V;

Ue:

AC110/130V, AC230/240V, AC380V, AC400/415V, AC440V, AC550V,

DC250V(2P in series), DC125V(1P in series);

In:100A, 125A, 150A, 160A, 175A, 200A,225A, 250A;

Overcurrent release: Thermo-magnetic;

Icu:

Type F: 25kA(AC110/130/230/240V), 18kA(AC380/400/415V),

15kA(AC440V), 5kA(AC550V,DC250V,DC125V)

Type N: 50kA(AC110/130/230/240V), 25kA(AC380/400/415V),

20kA(AC440V,DC250V,DC125V), 8kA(AC550V),

Type H: 85kA(AC110/130/230/240V), 36kA(AC380/400/415V),

25kA(AC440V), 10kA(AC550V), 30kA(DC250V,DC125V)

Ics:

Type F: 13kA(AC110/130/230/240V), 9kA(AC380/400/415V),

8kA(AC440V), 3kA(AC550V,DC250V,DC125V)

Type N: 25kA(AC110/130/230/240V), 13kA(AC380/400/415V),

10kA(AC440V,DC250V,DC125V), 4kA(AC550V),

Type H: 43kA(AC110/130/230/240V), 18kA(AC380/400/415V),

13kA(AC440V), 5kA(AC550V), 15kA(DC250V,DC125V)

Selectivity category: A;

Suitable for insulation;

50/60Hz;

2P(only type H),3P

Page 1 of 1

Additional information (if necessary)

Date:

Apr.22,2021

Signature:



Lu Mei