

IEC**IECEE**

®

TM

Ref. Certif. No.

CN50818-M1/A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Moulded Case Circuit-breaker

Name and address of the applicant

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the manufacturer

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

Schneider (Thailand) Limited
540 Soi 9 Bangpoo Industrial Estate, Sukhumvit Road, Muang
District, Samutprakarn 10280, Thailand*Note: When more than one factory, please report on page 2*

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

EZC100B, EZC100F, EZC100N, EZC100H

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016(5th Edition); IEC
60947-2:2016/AMD1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2020CQC-090852-M1

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Dec.21,2020

Signature:

Lu Mei

CB 0059032

EZC100B, EZC100F, EZC100N, EZC100H

Ui:690V;

Uimp:6kV;

Over-current release: Thermal Magnetic;

Selectivity category: A;

Rated frequency:50/60Hz;

Applicable for isolation

Type		EZC100B	EZC100F	EZC100N		EZC100H	
number of poles		3P	3P	1P	3P, 4P	1P	2P, 3P, 4P
In (A)		15, 16, 20, 25, 30, 32, 40, 45, 50, 60	15, 16, 20, 25, 30, 32, 40, 45, 50, 60, 63, 75, 80, 100				
Icu (kA)	AC 110/130V	10	25	25	25	50	100
	AC 220/230/240V	10	25	18	25	25	50 (2P)/ 100 (3P, 4P)
	AC 380V	7,5	10	2,5	18	5	30
	AC 400/415V	7,5	10	2,5	15	5	30
	AC 440V	5	7,5	-	10	-	20
	AC 550V	2,5	5	-	5	-	10
	DC 125V (1P)	-	5	5	5	10	10
	DC 250V (2P in series)	-	5	-	5	-	10
Ics (kA)	110-400V	25% Icu	50% Icu	50% Icu	50% Icu	50% Icu	50% Icu
	415-550V						25% Icu

Additional information (if necessary)

Date: Dec.21,2020

Signature:



Lu Mei