

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switch-disconnector

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, rue Joseph Monier, 92500 RUEIL MALMAISON - France

Name and address of the manufacturer

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendes France,
Eybens - 38050 GRENOBLE Cedex 9 - France

Name and address of the factory

SCHNEIDER ELECTRIC Alpes
Voie Isaac Newton ZI Alpespace, 73800 FRANCIN
France

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

NW40bHA, NW50 HA, NW63 HA

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60947-1:2007(ed.5) +A1:2010 +A2:2014
IEC 60947-3:2008 (ed.3) +A1:2012 +A2:2015

As shown in the Test Report Ref. No. which forms part of this Certificate

160119940024-00 to 160119940024-02,
160119940025-00, 160119940025-01

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 24/02/2017

Signature: **Jean-François BRUEL**
Certification Officer


ANNEX
References, ratings and main characteristics

| Type | I _e (A) | Poles |
|----------|--------------------|--------|
| NW-40bHA | 4000 | 3P, 4P |
| NW-50HA | 5000 | 3P, 4P |
| NW-63HA | 6300 | 3P, 4P |

| | |
|---|---|
| - method of operation | Independent manual and power operation |
| - suitability for isolation | Suitable |
| - number of poles | 3P,4P |
| - kind of current | AC |
| -in the case of a.c., number of phases and rated frequency | 3 phases, 50/60Hz |
| Rated and limiting values, main circuit | |
| - rated operational voltage U _e (V) | 220...690Vac |
| - rated insulation voltage U _i (V) | 1000V |
| - rated impulse withstand voltage U _{imp} (kV) | 12kV |
| - conventional free air thermal current I _{th} (A) | 4000A, 5000A, 6300A |
| - rated operational current I _e (A) | 4000A, 5000A, 6300A |
| - rated uninterrupted current I _u (A) | 4000A, 5000A, 6300A |
| - rated frequency (Hz) | 50/60Hz |
| - utilization category | AC-23A |
| Short-circuit characteristic | |
| - rated short-time withstand current I _{cw} (kA) | 85kA/3s |
| - rated short-time making capacity I _{cm} (kA) | 187kA |
| Control circuits | AC: 24-48V, 100/130V, 200/250V, 277-380/480V DC: 12-24/30V, 48/60V, 100/125V, 200/250V |



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Signature: **Jean-François BRUEL**
Certification Officer

Date: 21/02/2017