


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC ESPAÑA, S.A. Camino Barranquet, 57 46133 Meliana (Valencia) Spain
<i>Note: When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	1P+N – Un = 230 V – Curves B and C In = 4, 6, 10, 13, 16, 20, 25, 32 or 40 A – type A, Asi or AC IΔn = 10, 30 or 300 mA – Icn = 6000 A – IΔm = 3000 or 4500 A (see pages 4, 6, 7 and 8 of Test Report PB17-0011730-03-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series DPN Vigi (see Additional Sheet)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61009-1:2010, IEC 61009-1:2010/AMD1:2012, IEC 61009-1:2010/AMD2:2013, IEC 61009-2-1:1991
As shown in the Test Report Ref. No. which forms part of this Certificate	PB17-0011730-03-00 and from PB17-0011730-03-01 to PB17-0011730-03-30

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-I-20138 Milano, Italy



Description of RCBOs Series DPN Vigi ($I_{cn} = 6000 \text{ A}$)

Generic reference ⁽¹⁾	Curve	I_n	Type ⁽²⁾	$I_{\Delta n}$	Colour of handle
P1B60004AC30	B	4 A	AC	30 mA	Black, orange, white or blue lavender
P1B60006AC30	B	6 A	AC	30 mA	Black, orange, white or blue lavender
P1B600010AC30	B	10 A	AC	30 mA	Black, orange, white or blue lavender
P1B600013AC30	B	13 A	AC	30 mA	Black, orange, white or blue lavender
P1B600016AC30	B	16 A	AC	30 mA	Black, orange, white or blue lavender
P1B600020AC30	B	20 A	AC	30 mA	Black, orange, white or blue lavender
P1B600025AC30	B	25 A	AC	30 mA	Black, orange, white or blue lavender
P1B600032AC30	B	32 A	AC	30 mA	Black, orange, white or blue lavender
P1B600040AC30	B	40 A	AC	30 mA	Black, orange, white or blue lavender
P1B60004AC300	B	4 A	AC	300 mA	Black, orange, white or blue lavender
P1B60006AC300	B	6 A	AC	300 mA	Black, orange, white or blue lavender
P1B600010AC300	B	10 A	AC	300 mA	Black, orange, white or blue lavender
P1B600013AC300	B	13 A	AC	300 mA	Black, orange, white or blue lavender
P1B600016AC300	B	16 A	AC	300 mA	Black, orange, white or blue lavender
P1B600020AC300	B	20 A	AC	300 mA	Black, orange, white or blue lavender
P1B600025AC300	B	25 A	AC	300 mA	Black, orange, white or blue lavender
P1B600032AC300	B	32 A	AC	300 mA	Black, orange, white or blue lavender
P1B600040AC300	B	40 A	AC	300 mA	Black, orange, white or blue lavender
P1B60004A30	B	4 A	A	30 mA	Black, orange, white or blue lavender
P1B60006A30	B	6 A	A	30 mA	Black, orange, white or blue lavender
P1B600010A30	B	10 A	A	30 mA	Black, orange, white or blue lavender
P1B600013A30	B	13 A	A	30 mA	Black, orange, white or blue lavender
P1B600016A30	B	16 A	A	30 mA	Black, orange, white or blue lavender
P1B600020A30	B	20 A	A	30 mA	Black, orange, white or blue lavender
P1B600025A30	B	25 A	A	30 mA	Black, orange, white or blue lavender

Generic reference ⁽¹⁾	Curve	I _n	Type ⁽²⁾	I _{Δn}	Colour of handle
P1B600032A30	B	32 A	A	30 mA	Black, orange, white or blue lavender
P1B600040A30	B	40 A	A	30 mA	Black, orange, white or blue lavender
P1B60004A300	B	4 A	A	300 mA	Black, orange, white or blue lavender
P1B60006A300	B	6 A	A	300 mA	Black, orange, white or blue lavender
P1B600010A300	B	10 A	A	300 mA	Black, orange, white or blue lavender
P1B600013A300	B	13 A	A	300 mA	Black, orange, white or blue lavender
P1B600016A300	B	16 A	A	300 mA	Black, orange, white or blue lavender
P1B600020A300	B	20 A	A	300 mA	Black, orange, white or blue lavender
P1B600025A300	B	25 A	A	300 mA	Black, orange, white or blue lavender
P1B600032A300	B	32 A	A	300 mA	Black, orange, white or blue lavender
P1B600040A300	B	40 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C4AC30	C	4 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C6AC30	C	6 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C10AC30	C	10 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C13AC30	C	13 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C16AC30	C	16 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C20AC30	C	20 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C25AC30	C	25 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C32AC30	C	32 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C40AC30	C	40 A	AC	30 mA	Black, orange, white or blue lavender
P1B6000C4AC300	C	4 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C6AC300	C	6 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C10AC300	C	10 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C13AC300	C	13 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C16AC300	C	16 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C20AC300	C	20 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C25AC300	C	25 A	AC	300 mA	Black, orange, white or blue lavender

Generic reference ⁽¹⁾	Curve	I _n	Type ⁽²⁾	I _{Δn}	Colour of handle
P1B6000C32AC300	C	32 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C40AC300	C	40 A	AC	300 mA	Black, orange, white or blue lavender
P1B6000C4A30	C	4 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C6A30	C	6 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C10A30	C	10 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C13A30	C	13 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C16A30	C	16 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C20A30	C	20 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C25A30	C	25 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C32A30	C	32 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C40A30	C	40 A	A	30 mA	Black, orange, white or blue lavender
P1B6000C4A300	C	4 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C6A300	C	6 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C10A300	C	10 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C13A300	C	13 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C16A300	C	16 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C20A300	C	20 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C25A300	C	25 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C32A300	C	32 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C40A300	C	40 A	A	300 mA	Black, orange, white or blue lavender
P1B6000C4Asi30	C	4 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C6Asi30	C	6 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C10Asi30	C	10 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C13Asi30	C	13 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C16Asi30	C	16 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C20Asi30	C	20 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C25Asi30	C	25 A	Asi	30 mA	Black, orange, white or blue lavender

Generic reference ⁽¹⁾	Curve	I_n	Type ⁽²⁾	$I_{\Delta n}$	Colour of handle
P1B6000C32Asi30	C	32 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C40Asi30	C	40 A	Asi	30 mA	Black, orange, white or blue lavender
P1B6000C4Asi300	C	4 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C6Asi300	C	6 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C10Asi300	C	10 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C13Asi300	C	13 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C16Asi300	C	16 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C20Asi300	C	20 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C25Asi300	C	25 A	Asi	300 mA	Black, orange, white or blue lavender
P1B6000C32Asi300	C	32 A	Asi	300 mA	Black, orange, white or blue lavender

(1) – The general reference may be completed with a letter indicating the colour of the case, as follows:

blank = grey case

b = white case

(2) – “Asi”-type RCBOs are A-type RCBOs having an intentional short-time delay