



Certificate of Compliance

Certificate: 2700183

Master Contract: 225619

Project: 80042600

Date Issued: May 11, 2020

Issued to: Telemecanique/Schneider Electric Industries SAS
BP 660, Zone Industrielle No. 3
L'Isle d'Espagnac, 16340
FRANCE
Attention: Mr. Jean-Pierre Laidet

The products listed below are eligible to bear the CSA Mark shown



Issued by: *Edwin Chao*
Edwin Chao

PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT - Miscellaneous Apparatus

Electromagnetic relays, open type, plug-in with socket, DIN-rail mounted:

Cat. No. RUM, followed by C or F, followed by 2 or 3, followed by 1, 2 or 3, followed by E7, F7, P7, B7, FD, GD, JD, MD, BD, ED or ND, maybe followed by additional numbers;

Cat. No. 750, followed XBXR or XCXR, maybe followed by C, maybe followed by M4 and/or L, followed by 6A, 12A, 24A, 48A, 120A, 230A, 240A, 6D, 12D, 24D, 48D, 60D, 110D, 125D or 220D, maybe followed by additional numbers;

Cat. No. 788, followed XBXR or XCXR, maybe followed by 69, maybe followed by C or C1, maybe followed by M4 and/or L1, followed by 6A, 12A, 24A, 48A, 120A, 230A, 240A, 12D, 24D, 48D, 60D, 110D, 125D or 220D, maybe followed by additional numbers.

Coil voltage:

RUMC2: 24, 48, 120 or 230 Vac; 12, 24, 48 or 110 Vdc

RUMC3: 24, 48, 120 or 230 Vac; 12, 24, 48, 60, 110, 125 or 220 Vdc

RUMF: 24, 48, 120 or 230 Vac; 12, 24, 48, 60, 110, 125 or 220 Vdc

750XBXR: 6, 12, 24, 48, 120 or 240 Vac; 6, 12, 24, 48 or 110 Vdc

750XCXR: 24, 48, 120 or 240 Vac; 12, 24, 48 or 110 Vdc

788XBXR: 24, 48, 120 or 240 Vac; 12, 24, 48 or 110 Vdc

788XCXR: 12, 24, 48, 120 or 240 Vac; 12, 24, 48 or 110 Vdc



Certificate: 2700183
Project: 80042600

Master Contract: 225619
Date Issued: May 11, 2020

Contacts rating:

RUM, 750, 788 (except 788XBR69) with 2 or 3 NO/NC (Form C): 277 Vac or 30 Vdc, 10 A resistive (200,000 cycles); 120 Vac, 1/3 hp motor (6,000 cycles); 277 Vac, 1 hp motor (6,000 cycles); B300 code (6,000 cycles)
788XBR69 with 2 NO/NC (Form C): 277 Vac or 30 Vdc, 10 A resistive (200,000 cycles); 120 Vac, 1/3 hp motor (6,000 cycles); 277 Vac, 1 hp motor (6,000 cycles); B300 code (6,000 cycles); 150 Vdc, 5 A general use (6,000 cycles)

Notes:

1. The relays and sockets are certified as open type devices for use only in other certified equipment where the suitability of the combination is to be determined by CSA.
2. The devices have been evaluated as open type at (surrounding air) temperature 55°C max.

APPLICABLE REQUIREMENTS

CSA-C22.2 No.14-18 - Industrial Control Equipment



Supplement to Certificate of Compliance

Certificate: 2700183

Master Contract: 225619

The products listed, including the latest revision described below, are eligible to be marked in accordance with the referenced Certificate.

Product Certification History

Project	Date	Description
80042600	2020-05-11	Update report 2700183 to include the alternate polymeric materials and internal soft wiring; Update the dimensions and manufacturer name for various parts.
70214978	2019-07-03	Update report for alternate manufacturer of Soft Wire (Accepted, Recognized component), and to CSA C22.2 No. 14-18 (Cert. Notice-Ind. Control Equip. No. 60)
2700183	2014-02-27	CSA Certification of Electromagnetic relays, Cat. Nos. RUM or 750 or 788 (with suffixes), 2 or 3 contacts (NO/NC, Form C).