

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product	Enclosures for pre-determined equipment for household and similar fixed electrical installations
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIE ITALIA S.p.A. Via Circonvallazione Est, 1 24040 – Stezzano (BG) Italy
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC INDUSTRIE ITALIA S.p.A. Via Circonvallazione Est, 1 24040 – Stezzano (BG) Italy
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Surface mounting enclosures; -25 °C to +60 °C; IP40; rated current = 50 or 63 A; rated voltage = 230/400 V; rated insulation voltage = 400 V (see also pages 4 and 24 of Test Report MI17-0015348-01 and Additional Sheet)
Trademark (if any)	Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series MiniPragma (see Additional Sheet)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60670-1:2002, IEC 60670-1:2002/AMD1:2011, IEC 60670-24:2011
As shown in the Test Report Ref. No. which forms part of this Certificate	MI17-0015348-01

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43, IT-I-20138 Milano, Italy



**Description of surface mounting enclosures series MiniPragma**

<b>Type reference</b>	<b>Dimensions H × W × D (mm)</b>	<b>Number of modules / Number of DIN rail guides</b>	<b>Rated current (A)</b>
MIPS104 <i>or</i> MIPS104FR	198 × 124 × 95,5	4 / 1	50
MIPS106 <i>or</i> MIPS106FR	198 × 160 × 95,5	6 / 1	63
MIPS108 <i>or</i> MIPS108FR	198 × 196 × 95,5	8 / 1	63
MIPS112 <i>or</i> MIPS112FR	228 × 268 × 102	12 / 1	63
MIPS118 <i>or</i> MIPS118FR	228 × 376 × 103	18 / 1	63
MIPS124 <i>or</i> MIPS124FR	353 × 268 × 102	24 / 2	63
MIPS136 <i>or</i> MIPS136FR	478 × 268 × 102	36 / 3	63