



Ref. Certif. No.

ES2126**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER
WITHOUT INTEGRAL OVERCURRENT PROTECTION
(RCCB'S)

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, RUE JOSEPH MONIER
92506 RUEIL MALMAISON CEDEX (France)

Name and address of the manufacturer

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, RUE JOSEPH MONIER
92506 RUEIL MALMAISON CEDEX (France)

Name and address of the factory

SCHNEIDER ELECTRIC ESPAÑA, S.A.
CM BARRANQUET, 57
46133 MELIANA (Valencia - Spain)*Note: When more than one factory, please report on page 2* Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

B-IDD2P2510A-C; B-IDD2P2530A-C; B-IDD2P4030A-C; B-
IDD2P6330A-C; B-IDD4P4030A-C; B-IDD4P4030AG; B-IDD4P6330A-C;
B-IDD4P6330AC-CAdditional information (if necessary may also be
reported on page 2) Additional Information on page 2A sample of the product was tested and found
to be in conformity withIEC 61008-2-1:1990,
IEC 61008-1:2010,
IEC 61008-1:2010/A1:2012,
IEC 61008-1:2010/A2:2013As shown in the Test Report Ref. No. which forms part
of this CertificateGS134/18, GS131/18, GS132/18, GS198/18, GS135/18,
GS176/18, GS130/18, GS133/18

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
CI Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2018-10-31

Signature: 
Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES2126

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

PRODUCT: RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER WITHOUT INTEGRAL OVERCURRENT PROTECTION (RCCB'S)

Trade mark: SCHNEIDER ELECTRIC

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I Δ n	I Δ c	I Δ c	Type	Additional information
B-IDD2P2510A-C	2P	25 A	230/240 V~	10 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD2P2530A-C	2P	25 A	230/240 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD2P4030A-C	2P	40 A	230/240 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD2P6330A-C	2P	63 A	230/240 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD4P4030A-C	4P	40 A	400/415 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD4P4030AG	4P	40 A	400/415 V~	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	AG	Fuse 63 A gG (1)
B-IDD4P6330A-C	4P	63 A	400/415 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	A	Fuse 63 A gG (1)
B-IDD4P6330AC-C	4P	63 A	400/415 V~	30 mA	50 Hz	630 A	630 A	10000 A	10000 A	AC	Fuse 63 A gG (2)

These Residual current (RCCB's) should be protected by 63 A fuse type gG or Circuit-breakers.

(1)	Ambient temperature: -25/40 °C
(2)	Ambient temperature: -5/40 °C