

Schneider Electric
Reach Project

Date: 3/14/2012

Dear Customer,

As per the duties defined in article 33 of the REACH regulation N° 1907/2006, you will find attached below our best information regarding the presence of Substances of Very High Concern (called below SVHC) in the products of Schneider Electric.

The information below represents our best knowledge relative to the presence of SVHCs in our products as of the date of publication of this information.

This information will evolve over time, as a function of the improved knowledge resulting from both additional information provided by our suppliers and our own investigations.

In the context of the sustainable development policy of our Group, we continuously work towards products and services which reduce the impact to the environment or human health when used for their intended purpose and in conditions stated in the documentation provided by Schneider Electric.
At end of life, we recommend that you follow appropriate waste and recycling procedures.

Please Note: You can find more information about Schneider Electric environmental commitment on www.schneider-electric.com

Best Regards



Alain Digeon
SVP Reach Project
Schneider Electric

Schneider Electric

Schneider Electric SA
Mailing address:
35 rue Joseph Monier
92500 Rueil-Malmaison France
Phone: +33 (0)1 41 29 70 00
Fax: +33 (0)1 46 99 71 00

Legal information
Société anonyme with a management board and a supervisory board, with a registered capital of € 1,979,405,032
Registered Office: 35 rue Joseph Monier
92500 Rueil-Malmaison France
542 048 574 r.c.s. Nanterre

The data shown in this spreadsheet are related to the following production Date Code: 1201

The data shown in this spreadsheet are related to the following version of the REACH regulation: Dec 2011 candidate list

Commercial ref.	SVHC content	
Range Brand	Product description	
G3HT10K3IB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:1 with 10min Battery, Start-up 5x8	
G3HT10K3IB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:1 with 30min Battery, Start-up 5x8	
G3HT10K3ILS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:1 with Long Backup Charger, Start-up 5x8	

G3HT10K3IS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:1, Start-up 5x8	
G3HT10KHB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:3 with 10min Battery, Start-up 5x8	
G3HT10KHB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:3 with 30min Battery, Start-up 5x8	
G3HT10KHLS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:3 with Long Backup Charger, Start-up 5x8	

G3HT10KHS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 10kVA 400V 3:3, Start-up 5x8	
G3HT15K3IB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:1 with 10min Battery, Start-up 5x8	
G3HT15K3IB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:1 with 30min Battery, Start-up 5x8	
G3HT15K3ILS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:1 with Long Backup Charger, Start-up 5x8	

G3HT15K3IS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:1, Start-up 5x8	
G3HT15KHB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:3 with 10min Battery, Start-up 5x8	
G3HT15KHB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:3 with 30min Battery, Start-up 5x8	
G3HT15KHLS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:3 with Long Backup Charger, Start-up 5x8	

G3HT15KHS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 15kVA 400V 3:3, Start-up 5x8	
G3HT20K3IB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:1 with 10min Battery, Start-up 5x8	
G3HT20K3IB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:1 with 25min Battery, Start-up 5x8	
G3HT20K3ILS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:1 with Long Backup Charger, Start-up 5x8	

G3HT20K3IS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:1, Start-up 5x8	
G3HT20KHB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:3 with 10min Battery, Start-up 5x8	
G3HT20KHB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:3 with 25min Battery, Start-up 5x8	
G3HT20KHLS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:3 with Long Backup Charger, Start-up 5x8	

G3HT20KHS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 20kVA 400V 3:3, Start-up 5x8	
G3HT30K3IB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:1 with 10min Battery, Start-up 5x8	
G3HT30K3IB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:1 with 25min Battery, Start-up 5x8	
G3HT30K3ILS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:1 with Long Backup Charger, Start-up 5x8	

G3HT30K3IS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:1, Start-up 5x8	
G3HT30KHB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:3 with 10min Battery, Start-up 5x8	
G3HT30KHB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:3 with 25min Battery, Start-up 5x8	
G3HT30KHLS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:3 with Long Backup Charger, Start-up 5x8	

G3HT30KHS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 30kVA 400V 3:3, Start-up 5x8	
G3HT40KHB1S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 40kVA 400V 3:3 with 10min Battery, Start-up 5x8	
G3HT40KHB2S 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 40kVA 400V 3:3 with 20min Battery, Start-up 5x8	
G3HT40KHLS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 40kVA 400V 3:3 with Long Backup Charger, Start-up 5x8	

G3HT40KHS 3Phase UPS APC	Dec. 2010 candidate list - 1 SVHC above the threshold	
	DEHP 117-81-7 rate (%) w/w 0.3%	
	MGE Galaxy 300 40kVA 400V 3:3, Start-up 5x8	