

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OCProduct
ProduitName and address of the applicant
Nom et adresse du demandeurName and address of the manufacturer
Nom et adresse du fabricantName and address of the factory
Nom et adresse de l'usineNote: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la deuxième pageRatings and principal characteristics
Valeurs nominales et caractéristiques principalesTrademark (if any)
Marque de fabrique (si elle existe)Model / Type Ref.
Ref. De typeAdditional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,
peuvent être indiqués sur la deuxième page)A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à laAs shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce CertificatThis CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification

Uninterruptible Power Supply

American Power Convers.Holding Inc. Taiwan Branch
4F, No. 205, Sec. 3, Beishin Rd.
Shindian City, Taipei, 231
TaiwanAmerican Power Convers.Holding Inc. Taiwan Branch
4F, No. 205, Sec. 3, Beishin Rd.
Shindian City, Taipei, 231
Taiwan Additional information on page 26A 230V 1Ø 50/60Hz
Output: Surge only outlets: 230V 50/60Hz
Battery backup outlets: 4.7A 230V 50/60Hz 1100VA, 660W
Total output current: 6A
Cl. I

BR1100CI...

The dots "." in the model name "." can be 0 to 9, A to Z, blank or "-", for
marketing use only. Additional information on page 2

IEC 62040-1-1(ed.1)

130423

This certificate replaces certificate NO42417/A1/M1, due to technical
modifications.Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 30-06-2009

Signature: Hanne Yndestad
Certification Department

American Power Conversion
Lot 3 Block 14 Phase 3, PEZA Cavite Economic Zone
Rosario Cavite
Philippines

APC India Pvt Ltd.
No. 18A, Survey No. 128, 1st Phase, Jigani Industrial Area,
Jigani Village, Jigani Hobli, Anekal Taluk, Bangalore-562106
India

International Precision Assemblies, Inc. (Plant 1)
Blk 8, Lot 6 East Avenue, Phase 1, CEPZA 4106
Rosario, Cavite
Philippines

International Precision Assemblies, Inc. (Plant 2)
Blk 17, Lot 2, Phase 4, CEPZA 4106
Rosario, Cavite
Philippines

Additional information(if necessary)
Information complémentaire (si nécessaire)




Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 30-06-2009

Hanne Yndestad

Signature: Hanne Yndestad
Certification Department

	<p>Test Report issued under the responsibility of:</p>  <p>www.nemko.com</p>
<p>Amendment to Test Report This Amendment is valid only together with the main Test Report</p>	
<p>Report Reference No : 130423 Main Report Reference No : 80748 Tested by : Andy Lee (printed name and signature) :  Approved by : Roger Liou (printed name and signature) : </p> <p>Date of issue : June 29, 2009</p>	
<p>Testing Laboratory Name : Nemko Taiwan Phone: (+886) 2 8797 8790 Address : 5 Fl., No. 409, Sec. 2, Tiding Blvd., Neihu, Taipei 114, Taiwan Testing location : CBTL <input checked="" type="checkbox"/> CCATL <input type="checkbox"/> SMT <input type="checkbox"/> TMP <input type="checkbox"/> Address : Same as above</p>	
<p>Applicant's Name : American Power Conversion Holding Inc. Taiwan Branch Address : 4F, No. 205, Section 3, Beishin Rd., Shindian City, Taipei, 231, Taiwan</p>	
<p>Test specification</p> <p>Standard..... : IEC 62040-1-1:2002 (1st Edition) Test procedure : CB/CCA-scheme Non-standard test method : N/A</p>	
<p>Test Report Form No. : IEC62040_1_1A TRF originator : SGS Fimko Ltd Master TRF : dated 2003-03</p> <p>Copyright © 2002 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved. This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.</p>	
<p>Test item description : Uninterruptible Power Supply Trademark : </p> <p>Manufacturer : Same as applicant Model and/or type reference : BR1100CI... (The dots in the model name "." can be 0 to 9, A to Z , blank or "-", for marketing use only) Serial number : Test sample without serial numbers Rating(s)..... : AC input: 6A 230V 50/60Hz 1Ø Class I Output: Surge only outlets: 230V 50/60Hz Battery backup outlets: 4.7A 230V 50/60Hz 660W 1100VA Total output current: 6A</p>	

Rev. 2007-06 KS