



CERTIFICATE FI 30183 A1

Our Ref. 290669

Product Plug and Outlet for lampfitting

Type DCL plug BBV58748

Trade mark Schneider Electric

Certificate Holder Schneider Electric Industries SAS
35, rue Joseph Monier, 92500 RUEIL MALMAISON,
FRANCE

Manufacturer Schneider Electric Industries SAS
35, rue Joseph Monier, 92500 RUEIL MALMAISON,
FRANCE

Technical information 6 A, 250 V~

Other information Rewirable for flexible cable 3G0.5-1.0mm². Screw terminals. Standard sheet 1-2.
See the appendix for variants

The product is certified according to the following standard(s) EN 61995-1:2008 + A1:2017
EN 61995-2:2009 + A1:2017

Validity This certificate is valid until 06 November 2022 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that product changes (if any) will be approved at SGS Fimko before the product is brought onto market.

Directive information The certified product(s) fulfils requirements of above mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.


Date of issue 12 March 2018

SGS Fimko Ltd

Signature

Matti Huttunen
Certification Engineer

This certificate has 1 appendix



This certificate is issued by the company under its General Conditions for Certification Services accessible at <http://www.sgs.fi/en/Terms-and-Conditions.aspx>. Attention is drawn to the limitations of liability defined therein and in the Test Report here above mentioned which findings are reflected in this certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Manufacturing sites

Elda-Eltra Elektrotechnika S.A
ul. Bugno 1, 78-400 SZCZECINEK,
POLAND

Lexel Fabrika SIA
Krustpils 35a, LV-1073 RIGA,
LATVIA

Additional information

The product has certificate P17222384/A1 issued by Nemko AS in accordance with the Nordic Certification Service system.



DCL Outlet and DCL Plug

1

DCL Wall; Couplers: 15003 (Screw terminals) QGH60131 and QGH60133 (Screwless terminals); Covers: SIA88392 (Exxact design) QGH1235602 (Renova design)

6A 250V AC

DCL outlet and DCL plug. Flush type, rewirable, for rigid (stranded) conductors 1.0-2.5mm². Mounting in wall boxes with 60mm fixing distance. Standard sheet 1-1 and 1-2

DCL Outlet and DCL Plug

2

DCL Ceiling; Couplers: 15003 (Screw terminals) QGH60131 and QGH60133 (Screwless terminals); Covers: SIA88421 (inner center cover - Exxact design) SIA88397 (outer center cover - Exxact design) QGH1131302

6A 250V AC

DCL outlet and DCL plug. Flush type, rewirable, for rigid (stranded) conductors 1.0-2.5mm². Mounting in ceiling boxes with 70mm fixing distance, a 10mm spacer can be fitted, equipped with device (hook) for hanging up to 15kg. Standard sheet 1-1 and 1-2.

DCL Outlet and DCL Plug

3

DCL spacer: WDE005103 (Exxact design)

Frame for making additional space for DCL ceiling

DCL Outlet and DCL Plug

4

DCL Wall; Coupler: QGH57336 (Screwless terminals), Covers: QGH1235702 (Exxact design)

6A 250V AC

DCL Outlet. Flush type. Rewirable for rigid (stranded) conductors 1.0-2.5mm². Mounting in wall boxes with 60mm fixing distance. Standard sheet 1-1 and 1-2

This certificate replaces previous certificate FI 30183 dated 06 November 2017. A new variant has been added.

Our ref. no.

290669-3