


# CERTIFICATE FI/41656

Our Ref. HEL-CERT230300551-01



**Product** Shuttered socket-outlet  
**Type** 101414-02, 101443-02, 101414  
**Trademark**   
**Certificate Holder** Schneider Electric Industries SAS  
35 Rue Joseph Monier, 92500, Rueil-Malmaison, France

**Technical information** 16 A, 250 V~, IP20, IP44

**Other information** Standard sheet III and I of SFS 5610  
Standard sheet I of NF C 61-314:2017  
Conductor area: 1,5 – 2,5 mm<sup>2</sup>

**General:**

In case the socket-outlet with unearthed fixing frame or plastic frame is to be installed in a metal box, the insulation p/n: BBV49557 shall be installed.

In case the socket-outlet with earthed fixing frame is to be installed in a metal box (box earthed) a clearance of minimum 3 mm shall be met.

**The product is certified according to the following standard(s)** IEC 60884-1:2002 + A1:2006 + A2:2013  
SFS 5610:2015 + A11:2016


**Validity** This certificate is valid until 2028-04-12 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

**Date of issue** 2023-04-12

**SGS Fimko Ltd**

**Signature**

  
Jonas Leinonen  
Certification Manager



**Manufacturer**

Schneider Electric Industries SAS  
35 Rue Joseph Monier, 92500, Rueil-Malmaison, France

**Manufacturing site**

Schneider Electric Elda S. A.  
Bugno 1, 78-400, Szczecinek, Poland

**Additional information**

Standard sheet III (SFS 5610) socket-outlets available build of parts (IP20 and IP44):

Part	Description
101414-02	insert base (Renova screw, Round screw)
101443-02	insert base (Exxact, Trend, Robust, Unica, new Unica, Odace, Ovalis)
101414	insert base (Exxact IP44 surface screwless / flush screw)
100977	insert cover & fixing part, screw-type (Exxact IP44), nature
101081	insert cover (Round), white
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw)(Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
101421	insert cover (screw + screwless) (Exxact)
101430	insert cover (screwless)(Exxact, Trend, System M, System Design, Robust)
100594	shutter slider natural / black
101037	shutter cassette body
101164	surface box (Exxact IP44), white
101164	surface box (Exxact IP44), black
101165	center plate SideE (Exxact IP44), white
101165	center plate SideE (Exxact IP44), black
101166/101167	lid (Exxact IP44), white
101166/101167	lid (Exxact IP44), black
101155	center plate SideE (Round), white
101367, 101364	Center plate SideE (Renova), white
101367, 101364	center plate SideE (Renova), black
101392	center plate SideE (Trend)
101527	center plate SideE (Unica)
101531	center plate SideE (Unica)
101604	center plate SideE (Robust surface)
101610	center plate SideE (Robust flush)
BBV35087	center plate SideE (Exxact high, full-flush), white
BBV35087	center plate SideE (Exxact high, full-flush), black & black +painted
BBV35087	center plate SideE (Exxact low, semi flush), white
BBV35087	center plate SideE (Exxact low, semi flush), black & black +painted
BBV111557	center plate SideE (Exxact), white
BBV4013402	center plate SideE (Odace), white / + painted alu
BBV42390	center plate SideE (Exxact), white
NHA44968	center plate SideE (M-SMART, full-flush), white
NHA44968	center plate SideE (M-SMART, full-flush), active white & ivory
NHA44972	center plate SideE (M-SMART, semi flush), white
NHA44972	center plate SideE (M-SMART, semi flush), active white & ivory
S1B67876	center plate SideE (Exxact), white / painted met or anthr.
S1B13009	center plate unearthed / SideE (Exxact), white
BBV49557	Insulation

**Additional information**

Standard sheet I (SFS 5610) socket-outlets available build of parts (IP20):

Part	Description
101414-02	Insert base
101443-02	Insert base
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw) (Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
101430	insert cover (screwless) (Exxact, Trend, System M, System Design, Robust)
100594	shutter slider natural / black
101037	shutter cassette body
BBV49557	Insulation
100465	center plate unearthed (Trend)
101528	center plate unearthed (Unica)
101365, 101364	center plate unearthed (Renova)
101532	center plate unearthed (Unica)
BBV42385	center plate unearthed (Exxact)
S1B13009	center plate unearthed / SideE (Exxact)


Standard sheet I (NF C 61-314:2017) socket-outlets available build of parts (IP20):

Type number	Description
101414-02	insert base (Renova screw, Round screw)
101443-02	insert base (Exxact, Trend, Robust, Unica, new Unica, Odace, Ovalis)
101081	insert cover (Round)
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw) (Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
100594	shutter slider natural / black
101037	shutter cassette body
101530	center plate PinE PO/FR (Unica)
101533	center plate PinE CZ (Unica)
101535	center plate PinE CZ (Unica)
NVE8058402	center plate PinE FR (new Unica), white / painted alu/ graphite
S1A6508002	center plate PinE FR (Ovalis), white
BBV5354402	center plate PinE FR (Odace), white / + painted alu
BBV49557	Insulation

Socket-outlets according to the standard sheet I of NF C 61-314:2017 are not suitable for use in Finland.

The products have certificate no. SE-S-2300261 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.

**As shown in the Test Report(s) No(s):** 2300701STO-001, 2300701STO-002, 2300701STO-003



This document is issued by the Company under its General Conditions of Service accessible at [http://www.sgs.com/terms\\_and\\_conditions.htm](http://www.sgs.com/terms_and_conditions.htm). Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.