



Ref. Certif. No.

DK-117783-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Energy Meter/Power Meter
Name and address of the applicant	SCHNEIDER ELECTRIC PVT LTD 12A ATTIBELE INDUSTRIAL AREA NERALUR (PO), KARNATAKA 562107 INDIA
Name and address of the manufacturer	SCHNEIDER ELECTRIC PVT LTD 12A ATTIBELE INDUSTRIAL AREA NERALUR (PO), KARNATAKA 562107 INDIA
Name and address of the factory	WUXI PRO-FACE ELECTRONICS CO LTD INDUSTRIAL DEVELOPMENT AREA 51-A WUXI NATIONAL HIGH-NEW TECH WUXI, JIANGSU, 214028 CHINA
Note: When more than one factory, please report on page 2	<input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Energy Meter (Measurement voltage) 3X100(173) to 3X277(480) Vac 50/60 Hz, 10 VA <input checked="" type="checkbox"/> Additional Information on page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	Energy Meter iEM3100, iEM3110, iEM3115, iEM3135, iEM3150, iEM3155, iEM3165, iEM3175 iEM3200, iEM3210, iEM3215, iEM3235, iEM3250, iEM3255, iEM3265, iEM3275 Power Meter PM3200, PM3210, PM3250, PM3255
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010, IEC 61010-1:2010/AMD1:2016, IEC 61010-2-030:2017
As shown in the Test Report Ref. No. which forms part of this Certificate	E360954-D1003-2/A0/C0-CB issued on 2021-05-24

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-09-16

Signature: Jan-Erik Storgaard



Ref. Certif. No.

DK-117783-UL

Additional Ratings:

Power Meter Control Power
100/173 - 277/480 V AC ($\pm 20\%$)
45 - 65 Hz, 3 W / 5 VA
100 - 300 V DC, 3W
Measurement voltage
60 - 277 V AC (Ph-N) ($\pm 20\%$)
100 - 480 V AC (Ph-Ph) ($\pm 20\%$)

Measurement current
iEM31XX series: 63 A maximum
iEM32XX series: 6 A maximum
PM32XX series: 6 A maximum

Additionally evaluated to:

EN 61010-1:2010/A1:2019
National Differences specified in the CB Test Report.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-09-16

Signature:

Jan-Erik Storgaard