

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Buzzer and Illuminated Buzzer
Name and address of the applicant	Schneider Electric Industries SAS 35 rue Joseph Monier Rueil Malmaison, 92500 France
Name and address of the manufacturer	Schneider Electric Industries SAS, Boulevard Salvador Allende, BP 660, 16340 L'isle D'espagnac France
Name and address of the factory	PT. Schneider Electric Manufacturing Batam Batam Industrial Park, Blk 1, 4 & 208, Mukakuning, Batam Indonesia <input type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	See Page 2
Trademark (if any)	Schneider Electric
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	XB5KS See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 60947-1:2007/A1:2011 and EN 60947-5-1:2017. National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-1(ed.5), IEC 60947-1(ed.5);am1, IEC 60947-5-1(ed.4)
As shown in the Test Report Ref. No. which forms part of this Certificate	4788189445 issued on 2018-02-06

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
 UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
 UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
 UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-02-27

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-70933-UL

Model Details:

XB5KS may be followed by 2, followed by B, G or M, may be followed by 4 or 8.

Ratings:

Electrical : PD3 OVC III AC/DC 50/60Hz

Type	Ue/Ui =	Ie / Ith =
Non illuminated	24 V ac/dc	Max 28mA
Non illuminated	110-120 V ac/dc	Max 20mA
Non illuminated	230-240 V ac	Max 18mA
Illuminated	24 V ac/dc	Max 58mA
Illuminated	110-120 V ac/dc	Max 20mA
Illuminated	230-240 V ac	Max 35mA

Mounting nut, torque 2.2 Nm

Field wiring : 22 – 16 AWG str.

IP : IP66, IP67

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-02-27

Signature:

Jan-Erik Storgaard