



CERTIFICATE FI/40546/A1

Our Ref. HEL-CERT200100028-02



Product Light dimmer

Type SBD 1-10V

Trademark 

Certificate Holder Schneider Electric Industries SAS
35 Rue Joseph Monier, 92500 Reuil-Malmaison,
France

Technical information 230 V AC, 400 W (incandescent lamps),
400 VA (electronic step-down converter for low-voltage halogen lamps),
50 Hz, IP20 / IP44 when using specific Exexact designs.

Other information Pattern No. 1, pillar, screw type terminals.
Electronic dimmer for electronic ballasts and transformers, flush mounting,
fuse F6,3AH and μ -disconnection.

The product is certified according to the following standard(s) EN 60669-1:1999 + A1:2002 + A2:2008
EN 60669-2-1:2004 + A1:2009 + A12:2010

Validity This certificate is valid until 23 January 2025 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 01 November 2023

SGS Fimko Ltd

Signature



Mikko Välimäki
Certification Manager

Page 1 of 3

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.



SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland
t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5

Member of the SGS Group (SGS SA)



Manufacturer Schneider Electric Industries SAS
35 Rue Joseph Monier, 92500 Rueil-Malmaison,
France

Manufacturing site GPV Estonia AS
Valga mnt. 7 A, EE-61504, Elva,
Estonia

Directive information The certified product(s) fulfils requirements of mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.

Additional information The products have certificate No. 1918694 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.

Cover design for inserts SBD 1-10V.
If the design includes frames sold separately the material is listed in column 3. All frames are from 1-5 gang.

Design	Reference Cover	Reference Frame
Trend	100949	100520
Trend Solid	100949	101543 (thermoplastic/glass/metallic)
Renova/Arezzo	101368	101370
Artic	13620	13601 (thermoplastic)
Artic Decor	13620	13806 (thermoplastic/glass/metallic)
Senso	20005157	20005048/20005050
Fashion	227010-0-1	21169.51-0:1
Riva	227010-0-1	204120-0-1
Scala	227010-0-1	21169.70-0:1
Novia	100634	100600 + 100601
Classic	227010-0-1	21169.151-0:1
Joy	267010-0-1	264100-0-1
MPLAN (System M)	5699	4861 (thermoplastic)
MPLAN II (System M)	5699	4881 (thermoplastic)
MPLAN metal (System M)	5699	4751 (metallic)
M-PLAN real glass (System M)	5699	4891 (real glass)
M-ARC (System M)	5699	4851 (thermoplastic)
M-STAR (System M)	5699	4871 (metallic)
Atelier-M (System M)	5699	3881 (thermoplastic)
1-M (System M)	5699	3891 (thermoplastic)
M-Smart (System M)	5699	4841 (thermoplastic/thermoset)
Elegance (System M)	5699	4021 (thermoplastic)
		4031 (metallic)
		4041 (glass)
		4051 (wood)

Additional information

Design	Reference Cover	Reference Frame
ARTEC	5720	4811 (thermoplastic/metallic/thermoset)
Antik	5720	4831 (thermoplastic/metallic)
D-Life	NHA5193102	NHA2920502 (thermoplastic) NHA2923102 (metal) NHA2922102 (glass/stone)
Forum	13620	W450104
Duet	-	-
Wessen 59	-	-
Exxact Primo	BBV39712	BBV49557 (gasket) BBV49583 (Primo IP44)
Exxact Basic	BBV39712	BBV49557 (gasket) BBV49550 (Basic IP44)
Exxact	BBV39712	Combi BBV49575 Basic BBV49550 Primo BBV49558 Solid BBV49558 Solid Glass S1A45091 Primo BBV49583 (IP2x)
Delo (Odace)	BBV4007302	BBV4007602 + S1A2148202
Unica	2004912	6.002.-

This certificate replaces previous certificate FI/40546, dated 2020-01-23, due to the factory's name change.

As shown in the Test Report(s) No(s): 1918694STO001