



Ref. Certif. No.

JPTUV-084471-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Uninterruptible Power Systems

Name and address of the applicant
Nom et adresse du demandeur

American Power Conversion Holding Inc., Taiwan Branch
3F., No. 205, Sec. 3, Beixin Rd.,
Xindian Dist. New Taipei City 231 Taiwan

Name and address of the manufacturer
Nom et adresse du fabricant

American Power Conversion Holding Inc., Taiwan Branch
3F., No. 205, Sec. 3, Beixin Rd.,
Xindian Dist. New Taipei City 231 Taiwan

Name and address of the factory
Nom et adresse de l'usine

VOLTRONIC POWER TECHNOLOGY CORP.
1-4F, Building 5, YuSheng Industrial
Park, No. 467, Section Xixiang, National Highway 107, Xixiang, Bao An
District, Shenzhen 518102, P. R. China

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Input : refer to test report
Output: refer to test report

Trademark (if any)
Marque de fabrique (si elle existe)

Schneider

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

N/A

Model / Type Ref.
Ref. de type

UPS: abc3Klde
(a, b, c, d and e= refer to the test report)
External battery cabinet: SRVS72BP-9A

Additional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la 2^{ème} page)

For model differences, refer to the test report
Re-issue of JPTUV-084471 dated 29.11.2017,
due to first modification.

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

IEC 62040-1:2008 +A1
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

50111071 002

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification



TÜV Rheinland Japan Ltd.
Global Technology Assessment Center
4-25-2 Kita-Yamata, Tsuzuki-ku
Yokohama 224-0021 Japan
Phone + 81 45 914-3888
Fax + 81 45 914-3354
Mail: info@jpn.tuv.com
Web: www.tuv.com

Date: 06.08.2018

Signature:


Sommy Chen



Test Report issued under the responsibility of:



TEST REPORT IEC 62040-1 Uninterruptible power systems (UPS) – Part 1: General and safety requirements for UPS	
Report Number.....	50111071 002
Date of issue.....	Aug. 03, 2018
Total number of pages.....	48 pages
Applicant's name.....	American Power Conversion Holdings Inc., Taiwan Branch
Address	3F., No. 205, Sec. 3, Beixin Rd., Xindian Dist. New Taipei City 231 Taiwan
Test specification:	
Standard	IEC 62040-1:2008 (First Edition) + Am 1:2013
Test procedure	CB Scheme
Non-standard test method	N/A
Test Report Form No.	IEC62040_1D
Test Report Form(s) Originator	TÜV Rheinland Japan Ltd.
Master TRF.....	Dated 2016-08
Copyright © 2016 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved. This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context. If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed. This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.	
General disclaimer:	
The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.	

Test item description:	Uninterruptible Power Systems
Trade Mark:	 by Schneider Electric or
Manufacturer:	Same as applicant
Model/Type reference:	UPS: abc3K1de (For variables a, b, c, d and e refer to page 12 for details) External battery cabinet: SRVS72BP-9A (trademark: Schneider) SRV72BP-9A (trademark: APC)
Ratings:	See page 12 for details.

1. Models definition:

UPS model type: abc3Klde		
Variable:	Range of variable:	Content:
a	SRV or SPV	a indicates different model name design, no affect safety.
b	S or blank	b indicates different trademark used on marking label, no affect safety, see pages 11-13 for details.
c	PM or nil	c indicates batteries configuration for UPS: nil means the UPS with internal batteries and without EBM; PM means the UPS without internal batteries and without EBM;
d	L or nil	d indicates different unit construction with or without internal batteries: L means long-term UPS type without internal batteries, blank means standard UPS type with internal batteries.
e	-AR, -GR, -RS, -SP, -KR, -BR, -CN or nil	e indicates different socket outlet type used: -AR means Argentina type outlet used; -GR, -RS, -SP, -KR means Schuko type outlet used; -BR means Brazil type outlet used; -CN means Chinese type outlet used; blank means IEC type outlet used;

2. Model differences:

Model type	Input rating	Output rating
abc3Klde	220-240Vac, 16A max. 50-60Hz; Icc: 1kA	220-240Vac, 50-60Hz, 13.6A max, 3kVA/2.4kW
SRVS72BP-9A, SRV72BP-9A	72VDC 50A	72VDC 50A

Component	Mains connection	Outlets
Model		
abc3Kld	C20 type inlet	C13 type and C19 type
abc3Kld-AR		Argentinean type
abc3Kld-BR		Brazil type
abc3Kld-CN		Chinese type
abc3Kld-GR, -RS, -SP, -KR,		Schuko type

Component	Input rating	Output rating	Outlet	Battery voltage	Dimension (W x H x D) (mm)	LOGO
-----------	--------------	---------------	--------	-----------------	----------------------------	------