

IEC**IECEE
CB
SCHEME**

Ref. Certif. No.

CN30625-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC**CB TEST CERTIFICATE**Product
Produit

AC Contactors

Name and address of the applicant
Nom et adresse du demandeurSchneider Shanghai Industrial Control Co.,Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.ChinaName and address of the manufacturer
Nom et adresse du fabricantSCHNEIDER ELECTRIC INDUSTRIES SAS
31, rue Pierre Mendès France - 38050 Grenoble Cedex 9 - FranceName and address of the factory
Nom et adresse de l'usineSCHNEIDER ELECTRIC INDIA Pvt. Ltd
Survey No.215, Village – Gagillapur Medak Road, Rangareddy
District, Hyderabad – 500 043, (A.P.) IndiaNote: When more than one factory, please report on page 2
Note: Lorsque plus d'une usinem, veuillez utiliser la 2^{me} pageRatings and principal characteristics
Valeurs nominales et caractéristiques principales

See the Appendix

Trademark (if any)
Marque de fabrique (si elle existe)

Schneider Electric

Model / Type Ref.
Ref. De type

LC1E06..., LC1E09..., LC1E12..., LC1E18...

Additional information (if necessary may also be reported
on page 2)
Les informations complémentaires (si nécessaire, peuvent être
indiqués sur la 2^{me} page)The Original CB certificate No. is CN30625,dated 2014-06-
04. The M1 certificate has been issued due to adding coil
voltage 230V.**PUBLICATION****EDITION**A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à laIEC 60947-4-1:2009(3rd Edition)+A1:2012, IEC 60947-
1:2007(5th Edition)+A1:2010As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constire partie de ce Certificat00901-CB2013CQC-056524, 00901-CB2015CQC-067112,
00901-CB2015CQC-067112-M1This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification****CHINA QUALITY CERTIFICATION CENTRE**

Date: 2015-09-29

Signature:

Wang Kejiao

Issued 2003-05
China Quality Certification Centre
Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.ChinaTel: +86-10-83886666
Fax: +86-10-83886282website
www.cqc.com.cn**CB 0033024**



Ref. Certif. No.

CN30625-M1

LC1E06..., LC1E09..., LC1E12..., LC1E18...

Ui: 690V;

LC1E06...:

Ith:20A;

AC-3:AC220/230/380V/6A,400/415V/4.9A;

AC-4:AC220/230/380V/5A,400/415V/4.1A;

LC1E09...:

Ith:25A;

AC-3:AC220/230/380V/9A,400/415V/8.5A;

AC-4:AC220/230/380V/7.5A,400/415V/7.1A;

LC1E12...:

Ith:25A;

AC-3:AC220/230/380V/12A,400/415V/11.5A;

AC-4:AC220/230/380V/10A,400/415V/9.6A;

LC1E18...:

Ith:32A;

AC-3:AC220/230/380V/18A,400/415V/15.5A;

AC-4:AC220/230/380V/15A,400/415V/13A;

Us:AC24V, 36V, 48V, 110V, 220V, 240V, 380V, 415V, 440V 50Hz;

AC24V, 110V, 220V, 380V, 440V 60Hz;

AC24V, 48V, 110V, 220V, 230V, 380V 50/60Hz;

3P;

IP20;

Auxiliary Circuits (body contact):

Ith:10A;

AC-15:AC380V/1.3A, 660V/0.75A;

DC-13:DC220V/0.3A;

1NO, 1NC

Additional information (if necessary)

Information complémentaire (si nécessaire)

Date: 2015-09-29

Signature:

Wang Kejiao