

CERTIFICATE

Issued to:
Applicant:
Schneider Electric The Netherlands B.V.
Taurusavenue 133
2132 LS Hoofddorp, The Netherlands

Licensee:
Schneider Electric Industries SAS Electropole
38EQI
Rue Francois Quesnay
38320 Eybens, France

Product : Residual current operated circuit-breaker (RCCB)
Trade name(s) : SCHNEIDER ELECTRIC
Type(s)/model(s) : IID

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61008-1:2012, EN 61008-1:2012/A1:2014, EN 61008-1:2012/A1:2014/AC:2016, EN 61008-1:2012/A2:2014, EN 61008-1:2012/A11:2015, EN 61008-1:2012/A12:2017, EN 61008-2-1:1994 and EN 61008-2-1:1994/A11:1998
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 900012


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 18 April 2019 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-107882

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



R Zhou
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Residual current operated circuit-breaker (RCCB)
Trade name(s)	: SCHNEIDER ELECTRIC
Type(s)/model(s)	: A9R01225, A9R01240, A9R01263, A9R01425, A9R01440, A9R01463, A9R04225, A9R04240, A9R04263, A9R04425, A9R04440 and A9R04463
Design	: functionally independent of line voltage
Behaviour to d.c. components	: type A
Method of mounting	: flush type for mounting on top hat rail
Grid distance	: 35 mm
Temperature limit	: -25 °C to +40 °C
Rated frequency	: 50 Hz
Rated impulse withstand voltage (Uimp)	: 4 kV
Type of terminal	: pillar terminals
Degree of protection	: IP20
Rated making and breaking capacity (Im)	: 1500 A
Rated residual making and breaking capacity (I Δ m)	: 1500 A
Rated conditional short-circuit current (Inc)	: 10 kA
Rated conditional residual short-circuit current (I Δ c)	: 10 kA
Protection against external influences	: enclosed
Method of mounting	: fixed installation; 35 mm rail

Product data – type A9R01225

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 25 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R01240

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 40 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R01263

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 63 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R01425

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 25 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

Product data – type A9R01440

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 40 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

Product data – type A9R01463

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 63 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

Product data – type A9R04225

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 25 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R04240

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 40 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R04263

Rated operational voltage (Un)	: 230 V~
Rated current (In)	: 63 A
Rated residual operating current (I Δ n)	: 30 mA
Number of poles	: 2P
Time delay	: without time delay

Product data – type A9R04425

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 25 A
Rated residual operating current (IΔn)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

Product data – type A9R04440

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 40 A
Rated residual operating current (IΔn)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

Product data – type A9R04463

Rated operational voltage (Un)	: 400 V~
Rated current (In)	: 63 A
Rated residual operating current (IΔn)	: 30 mA
Number of poles	: 4P
Time delay	: without time delay

TESTS**Test requirements**

EN 61008-1:2012
EN 61008-1:2012/A1:2014
EN 61008-1:2012/A1:2014/AC:2016
EN 61008-1:2012/A2:2014
EN 61008-1:2012/A11:2015
EN 61008-1:2012/A12:2017
EN 61008-2-1:1994
EN 61008-2-1:1994/A11:1998

Test result

The test results are laid down in DEKRA test file 223472800.

Additional information

This certificate replaces certificate No. 2160998.01 which we herewith declare invalid.

Conclusion

The examination proved that all requirements were met.

Factory location

Schneider Electric Espana S.A
Camino del Barranquet 57
46133 Meliana (VALENCIA), Spain