



IMPROVED CERTIFICATIONS SEARCH TOOL. REGISTER NOW!

[▶ LEARN MORE](#)

XBY57.E157293

Relocatable Power Taps Certified for Canada

[Page Bottom](#)

Relocatable Power Taps Certified for Canada

[See General Information for Relocatable Power Taps Certified for Canada](#)

SCHNEIDER ELECTRIC IT CORPORATION, FKA APC AMERICAN POWER CONVERSION

E157293

132 Fairgrounds Rd

PO BOX 278

West Kingston, RI 02892 USA

Relocatable Power Taps/ Surge Protective Devices, Type 3 SPDs, Model(s) P6U4*, P8*, PE6U4*, PE6U4W*, PE6U21*, PE6U21W*, **PH6U4X32+, PH6U4X32W+**

Relocatable Power Taps/ Surge Protective Devices, Type 3 SPDs, Model(s) PE6RU3, PE6RU3W

Relocatable power taps/surge protective devices, Model(s) P10U2*, P12U2*, P62SB*, P66SVB*, P6M*, P6M10*, P6TM*, P6TM10*

Relocatable power taps/surge protective devices, Type 3 SPD, Model(s) P66SS*

* - Complementary listed as Transient voltage surge suppressors, VZCA, under File E157293.

[Click here to view the Colombia Market Access Certification](#)

[Last Updated](#) on 2018-11-02

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2018 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2018 UL LLC".

**IMPROVED CERTIFICATIONS
SEARCH TOOL. REGISTER NOW!**[▶ LEARN MORE](#)**VZCA7.E157293
Surge-protective Devices Certified for Canada**[Page Bottom](#)**Surge-protective Devices Certified for Canada**[See General Information for Surge-protective Devices Certified for Canada](#)**SCHNEIDER ELECTRIC IT CORPORATION, FKA APC AMERICAN POWER CONVERSION**

E157293

132 Fairgrounds Rd
PO BOX 278
West Kingston, RI 02892 USA**Investigated to Other than CSA-C22.2 No. 269**

Model No.	SPD Type	Volts (V)	AC/DC/DC PV	PH	AMPS (A)	AMB (°C)Min	AMB (°C)Max	MODE	VPR (Vpk)	MCOV (V)	In (kA)	SCCR (kA)
Cord Connected												
P10U2+	3	120	AC	1	15	0	85	L-N L-G N-G	400 500 500	127 127 127	3	n/a
P62SB*, P66SVB*	3	120	AC	1	15	0	25	L-N L-G N-G	400 400 400	127 127 127	3	n/a
P66SS*	3	120	AC	1	15	0	25	L-N L-G N-G	400 500 400	127 127 127	3	n/a
P6M*, P6M10*	3	120	AC	1	15	0	25	L-N L-G N-G	400 400 400	127 127 127	3	n/a
P6TM*, P6TM10*	3	120	AC	1	15	0	25	L-N L-G N-G	400 400 400	127 127 127	3	n/a
P6U4*	3	120	AC	1	1	0	25	L-N L-G N-G	500 500 600	127 127 127	3	n/a
P8+	3	120	AC	1	15	0	25	L-N L-G N-G	330 400 400	127 127 127	3	n/a
PE6RU3+, PE6RU3W+	3	120	AC	1	15	0	25	L-N L-G N-G	500 500 500	127 127 127	3	n/a
PE6U4+, PE6U4W+, PE6U21+, PE6U21W+	3	120	AC	1	1	0	25	L-N L-G N-G	500 500 600	127 127 127	3	n/a
S9NC01RB20+	3	120	AC	1	15	0	25	L-N L-G N-G	330 400 400	127 127 127	3	n/a

Investigated to CSA C22.2 No. 269

Cat No.	SPD Type	Volts (V)	AC/DC/DC PV	PH	AMPS (A)	AMB (°C)Min	AMB (°C)Max	MODE	VPR (Vpk)	MCOV (V)	In (kA)	SCCR (kA)
PH6U4X32+, PH6U4X32W+	3	120	AC	1	15	0	25	L-N L-G N-G	400 500 500	127 127 127	3	N/A

These products are intended for installation on the line side (Type 1 SPD) or load side (Type 1, 2 or 3 SPDs) of the main service disconnect in circuits not exceeding 1000 V rms, and have been tested to verify that the transient-voltage surges are limited to the maximum amplitudes specified in the Voltage Protection Rating (VPR).

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

The effect of the surge-protective device on connected loads, the effect of the protector on harmonic distortion of the supply voltage, and the adequacy of the Voltage Protection Rating to protect connected equipment from damage from transient-voltage surges has not been determined.

* - Models Complementary Listed to XBYS, E157293.

+ - Complementary Listed to XBYS, XBYS7 E157293

Last Updated on 2018-11-02

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2018 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2018 UL LLC".