

CERTIFICATE

Issued to:

Applicant:

American Power Conversion Holdings Inc., Taiwan
Branch
5F., No. 189, Sec. 2, Jiuzong Rd., Neihu Dist.,
11494 Taipei City, Taiwan

Licensee:

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie
Town,
523963 Dongguan, Guangdong, China

Product : Multiple portable socket-outlets with SPD(s)
Trade name(s) : APC or APC by Schneider Electric
Type(s)/model(s) : PM6U-GR and PM6U-RS

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, IEC 60884-2-7:2011, IEC 60884-2-7:2011/A1:2013, EN 61643-11:2012, EN 61643-11:2012/A11:2018, NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019, NEN-IEC 60884-1:2019/A2:2019, EN IEC 62368-1:2020 and EN IEC 62368-1:2020/A11:2020
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2025917


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 20 January 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 35-121961

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



R Zhou
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Multiple portable socket-outlets with SPD(s)
Trade name(s)	: APC or APC by Schneider Electric
Type(s)/model(s)	: PM6U-GR and PM6U-RS
Rated current	: 16 A
Rated voltage	: 250 V~
Rated power	: MAX. 2500 W (Limited to 10 A by means of circuit breaker)
USB Output	: 5,0 V dc 2,4 A (Shared) 12,0 W
Earthing	: with side earthing-contacts
Design	: non-rewirable, with shutters
Standard sheet	: III of NEN 1020
Applied flexible cord	: H05VV-F 3G1,0 mm ²
Certification mark	: complies with the requirements
Cord termination	: soldered connection
Description	: body of thermoplastic material, 6-fold, provided with circuit-breaker, two-pole rocker switch, AC Surge Protective Device and dual port USB-Charger

TESTS**Test requirements**

IEC 60884-1:2002
IEC 60884-1:2002/A1:2006
IEC 60884-1:2002/A2:2013
IEC 60884-2-7:2011
IEC 60884-2-7:2011/A1:2013
EN 61643-11:2012
EN 61643-11:2012/A11:2018
NEN 1020:2019
NEN-IEC 60884-1:2019
NEN-IEC 60884-1:2019/A1:2019
NEN-IEC 60884-1:2019/A2:2019
EN IEC 62368-1:2020
EN IEC 62368-1:2020/A11:2020

Test result

The test results are laid down in DEKRA test file 610944100, 437709400, 437751600.

Additional information

The product also complies with Clause 10.5 of DIN VDE 0620-2-1:2021, BS EN 61643-11:2012 + A11:2018, BS EN 62368-1:2020 + A11:2020.

Remark: The type no. PM6U-RS is technically identical to the product PM6U-GR. The last two letters indicate the country code only.

The list of components is laid down in test report 4377516.50/51, 6109441.50, 4377094.50.

Conclusion

The examination proved that all requirements were met.

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
2nd Industrial Zone, Ju-Tang, Housha Road, Houjie Town,
523963 Dongguan, Guangdong, China