



CERTIFICATE

FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2002427R1

Junction box

Type designation:

TB32/42, TB77/SH53, TB50/SH26, 60/46

Certificate holder:

Schneider Electric Industries SAS
35 rue Joseph Monier FR 92500 Rueil-Malmaison
FRANCE

The product complies with the standard(s):

EN 60670-1:2005+A1:2013
EN 60670-21:2007

Date of expiry:

12 October, 2025

EU Directive information:

According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

Additional information in Appendix

Certification Body:

Intertek Semko AB, Product Certification

Place: Kista - Stockholm

Signed:


Date: 09 July, 2021

Quan Li

APPENDIX:

Reference No. SE-S-2002427R1


Technical Data:

Type designation 60/46
 Rated voltage (V) 450
 IP-Class IP30
 Standard sheet SS 430 06 17
 Trademark 


Test Report 2018926STO-001
 Product information Light grey or alternative Multifix Bio in white colour. Circular flush mounting box for accessory, for post mounting with inlets for 16 mm corrugated conduit. Temperature range -25/+90°C

Type designation TB32/42
 Rated voltage (V) 450
 IP-Class IP30
 Standard sheet SS 430 06 19
 Trademark 

Test Report 2018926STO-003
 Product information Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 32/42 with inner depth of 26 mm. Temperature range -25/+90°C.

Type designation TB50/SH26
 Rated voltage (V) 450
 IP-Class IP30
 Standard sheet SS 430 06 19
 Trademark 

Test Report 2018926STO-002
 Product information Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 50/SH26 with inner depth of 44 mm. Temperature range -25/+90°C.

Type designation TB77/SH53
 Rated voltage (V) 450
 IP-Class IP30
 Standard sheet SS 430 06 19
 Trademark 

Test Report 2105109
 Product information Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 77/53 with inner depth of 104 mm. Temperature range -25/+90°C.

APPENDIX:

Reference No. SE-S-2002427R1

Manufacturing Sites: Elda-Eltra Elektrotechnika S.A.
ul. Bugno 1
PL-78-400 Szczecinek
POLAND

Minera AS
Folmovegen 52
2150 Årnes
NORWAY

According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

This certificate replaces previously issued ref. No. SE-S-2002427 dated 12 Oktober 2020. A new certificate has been issued on account of addition of model TB77/SH53.

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed:



Date: 09 July, 2021

Quan Li

Intertek