

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0122-M1

AENOR, Spanish Association for Standardization and Certification, states that by request of:

SCHNEIDER ELECTRIC INDUSTRIES SAS

| | |
|--|---|
| registered office | 35, RUE JOSEPH MONIER 92506 RUEIL MALMAISON CEDEX (Francia) |
| a sample of the product | Residual current operated circuit-breaker without integral overcurrent protection (RCCB's) |
| has been tested and found to be in conformity with the standards | UNE-EN 61008-1:2013+A1:2015+A2:2015 (EN 61008-1:2012+A1:2014+A2:2014) UNE-EN 61008-2-1:1996+A11:1999 (EN 61008-2-1:1994+A11:1998) |
| Test report(s) | From GS173/15 to GS177/15, GS179/15, GS180/15, from GS182/15 to GS187/15, GS82/16 and GS105/16 |
| Trade mark | Schneider Electric Commercial name "RCCB Domae Biconnect" See annex for more information. |
| Manufactured at | Nº 172, Poonamalle Bye pass road, Poonamallee 600056 (Chennai - India) |
| Certification scheme | This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard. This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as revised on March 29th, 1983 and September 3rd, 2004. Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval as specified in OD 6, List of current decisions of CCA Group, point 2.11. |
| First issued on | 2016-06-14 |

AENOR Asociación Española de Normalización y Certificación

Avelino BRITO
Chief Executive Officer

AENOR

Asociación Española de Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 – www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0122-M1

Annex to Certificate

| Type Ref. | No. of poles | Rated current | Rated voltage | Rated residual current | Frequency | I _{Δm} | I _m | I _{nc} | I _{Δc} | Type | Additional information |
|------------------|--------------|---------------|---------------|------------------------|-----------|-----------------|----------------|-----------------|-----------------|------|------------------------|
| B-IDD2P1610AC | 2P | 16 A | 240 V- | 10 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P2510A | 2P | 25 A | 240 V- | 10 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P25100AC | 2P | 25 A | 240 V- | 100 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P2530A-A | 2P | 25 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | A | (1) |
| B-IDD2P2530A-B | 2P | 25 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P2530AC-A | 2P | 25 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P2530AC-B | 2P | 25 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P2530ASI | 2P | 25 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P25300AC-A | 2P | 25 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P25300AC-B | 2P | 25 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P25300ACS | 2P | 25 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P40100AC | 2P | 40 A | 240 V- | 100 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P4030A-A | 2P | 40 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P4030A-B | 2P | 40 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | A | (1) |
| B-IDD2P4030AC-A | 2P | 40 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P4030AC-B | 2P | 40 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P4030ASI | 2P | 40 A | 240 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P40300A | 2P | 40 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P40300AC-A | 2P | 40 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P40300AC-B | 2P | 40 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P40300ACS | 2P | 40 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P40300AS | 2P | 40 A | 240 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P40500AC | 2P | 40 A | 240 V- | 500 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P63100AC | 2P | 63 A | 240 V- | 100 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P6330A-A | 2P | 63 A | 240 V- | 30 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | A | (1) |
| B-IDD2P6330A-B | 2P | 63 A | 240 V- | 30 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | A | (1) |
| B-IDD2P6330AC-A | 2P | 63 A | 240 V- | 30 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P6330AC-B | 2P | 63 A | 240 V- | 30 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P63300A | 2P | 63 A | 240 V- | 300 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | A | (1) |
| B-IDD2P63300AC-A | 2P | 63 A | 240 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |

First issued on 2016-06-14

AENOR Asociación Española de Normalización y Certificación

AENOR

Asociación Española de Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 – www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0122-M1

Annex to Certificate

| Type Ref. | No. of poles | Rated current | Rated voltage | Rated residual current | Frequency | I _{Δm} | I _m | I _{nc} | I _{Δc} | Type | Additional information |
|------------------|--------------|---------------|---------------|------------------------|-----------|-----------------|----------------|-----------------|-----------------|------|------------------------|
| B-IDD2P63300AC-B | 2P | 63 A | 240 V- | 300 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |
| B-IDD2P63300ACS | 2P | 63 A | 240 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD2P63300AS | 2P | 63 A | 240 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | A | (1) |
| B-IDD4P25100AC | 4P | 25 A | 415 V- | 100 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P2530A | 4P | 25 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | A | (1) |
| B-IDD4P2530AC-A | 4P | 25 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P2530AC-B | 4P | 25 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P25300AC-A | 4P | 25 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P25300AC-B | 4P | 25 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P25500AC | 4P | 25 A | 415 V- | 500 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P40100AC-A | 4P | 40 A | 415 V- | 100 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P40100AC-B | 4P | 40 A | 415 V- | 100 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P4030A | 4P | 40 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | A | (1) |
| B-IDD4P4030A-B | 4P | 40 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD4P4030AC-A | 4P | 40 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P4030AC-B | 4P | 40 A | 415 V- | 30 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P40300A | 4P | 40 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | A | (1) |
| B-IDD4P40300AC-A | 4P | 40 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P40300AC-B | 4P | 40 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P40300AS | 4P | 40 A | 415 V- | 300 mA | 50 Hz | 500 A | 500 A | 3000 A | 3000 A | A | (1) |
| B-IDD4P40500AC | 4P | 40 A | 415 V- | 500 mA | 50 Hz | 500 A | 500 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P63100AC-A | 4P | 63 A | 415 V- | 100 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P63100AC-B | 4P | 63 A | 415 V- | 100 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P6330A | 4P | 63 A | 415 V- | 30 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | A | (1) |
| B-IDD4P6330A-B | 4P | 63 A | 415 V- | 30 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | A | (1) |
| B-IDD4P6330AC-A | 4P | 63 A | 415 V- | 30 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P6330AC-B | 4P | 63 A | 415 V- | 30 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |
| B-IDD4P63300A | 4P | 63 A | 415 V- | 300 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | A | (1) |
| B-IDD4P63300AC-A | 4P | 63 A | 415 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P63300AC-B | 4P | 63 A | 415 V- | 300 mA | 50 Hz | 630 A | 630 A | 6000 A | 6000 A | AC | (2) |

First issued on 2016-06-14

AENOR Asociación Española de Normalización y Certificación

AENOR

Asociación Española de Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 – www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0122-M1

Annex to Certificate

| Type Ref. | No. of poles | Rated current | Rated voltage | Rated residual current | Frequency | $I_{\Delta m}$ | I_m | I_{nc} | $I_{\Delta c}$ | Type | Additional information |
|-----------------|--------------|---------------|---------------|------------------------|-----------|----------------|-------|----------|----------------|------|------------------------|
| B-IDD4P63300ACS | 4P | 63 A | 415 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | AC | (2) |
| B-IDD4P63300AS | 4P | 63 A | 415 V- | 300 mA | 50 Hz | 630 A | 630 A | 3000 A | 3000 A | A | (1) |

Additional information

(1) -25°C to 40°C

(2) -5° C to 40°C

AENOR Asociación Española de
Normalización y Certificación

First issued on 2016-06-14