


CENELEC CERTIFICATION AGREEMENT

ACCORD DE CERTIFICATION DU CENELEC
CENELEC-ZERTIFIZIERUNGS-ABKOMMEN



STATEMENT OF TEST RESULTS

STR/2660/IMQ

Product	Circuit-breakers for overcurrent protection for household and similar installations
Tested by request of	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 – France
Manufactured at (name and place)	SCHNEIDER ELECTRIC THAILAND CO., LTD. 540 Soi 9 Bangpoo Industrial estate, Sukhmvit Road, Muang District 10280 Samutprakarn – Thailand or SCHNEIDER ELECTRIC BULGARIA EOOD Plovdiv plant – 4202 Radinovo – Bulgaria
Preliminary visit carried out by	—
Rating and principal characteristics	1P, 1P+N, 2P, 3P or 4P; Ue = 230/400 V (1P), 230 V (1P+N) or 400 V (2P, 3P and 4P); 50-60 Hz; Icn = 6000 A; Curve C; In = 6, 10, 13, 16, 20, 25 or 32 A (see also pages 6 and 7 of Test Report No. PB22-0080370-01-00 and/or Additional Sheet)
Trade mark (if any)	
Model/Type Ref.	iK60N series (see also page 7 of Test Report No. PB22-0080370-01-00 or Additional Sheet)
Additional information (if necessary)	—
A sample of the product has been tested and found to be in conformity with (HD/EN and equivalent national standard)	
• EN 60898-1:2019	
as shown in the test reports (reference No.)	PB22-0080370-01-00 and from PB22-0080370-01-01 to PB22-0080370-01-19

This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the above mentioned standard.

This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as amended on 29th March 1983 and September 3rd, 2004 (including addendum 1 dated July 1984, addendum 2 dated March 1987, addendum 3 dated September 1989 and addendum 4 dated March 1995). Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval, as specified in OD 6, List of current decisions of CCA Group, point 2.11.

IMQ S.p.A.

Milano, 2023-02-03

Signature of the authorized person _____

Name and function of the authorized person

Mauro Casari

**B.U. "Product Conformity Assessment"
"Project Management & Certification" Area
"Certification" Sector (voluntary field) - Manager**

Tel.: (+39) 02-50731
Fax.: (+39) 02-50991500
e-mail: info@imq.it

CENELEC CERTIFICATION AGREEMENT

ACCORD DE CERTIFICATION DU CENELEC

CENELEC-ZERTIFIZIERUNGS-ABKOMMEN



STATEMENT OF TEST RESULTS

Additional Sheet to STR/2660/IMQ

Generic reference of the circuit-breakers for overcurrent protection iK60N series and related ratings

Generic reference	Number of poles	Rated voltage	Curve	Rated current
iK60N 1P 6A C	1P	230/400 V	C	6 A
iK60N 1P 10A C	1P	230/400 V	C	10 A
iK60N 1P 13A C	1P	230/400 V	C	13 A
iK60N 1P 16A C	1P	230/400 V	C	16 A
iK60N 1P 20A C	1P	230/400 V	C	20 A
iK60N 1P 25A C	1P	230/400 V	C	25 A
iK60N 1P 32A C	1P	230/400 V	C	32 A
iK60N 1P+N 6A C	1P+N	230 V	C	6 A
iK60N 1P+N 10A C	1P+N	230 V	C	10 A
iK60N 1P+N 13A C	1P+N	230 V	C	13 A
iK60N 1P+N 16A C	1P+N	230 V	C	16 A
iK60N 1P+N 20A C	1P+N	230 V	C	20 A
iK60N 1P+N 25A C	1P+N	230 V	C	25 A
iK60N 1P+N 32A C	1P+N	230 V	C	32 A
iK60N 2P 6A C	2P	400 V	C	6 A
iK60N 2P 10A C	2P	400 V	C	10 A
iK60N 2P 13A C	2P	400 V	C	13 A
iK60N 2P 16A C	2P	400 V	C	16 A
iK60N 2P 20A C	2P	400 V	C	20 A
iK60N 2P 25A C	2P	400 V	C	25 A
iK60N 2P 32A C	2P	400 V	C	32 A
iK60N 3P 6A C	3P	400 V	C	6 A
iK60N 3P 10A C	3P	400 V	C	10 A
iK60N 3P 13A C	3P	400 V	C	13 A
iK60N 3P 16A C	3P	400 V	C	16 A
iK60N 3P 20A C	3P	400 V	C	20 A
iK60N 3P 25A C	3P	400 V	C	25 A
iK60N 3P 32A C	3P	400 V	C	32 A
iK60N 4P 6A C	4P	400 V	C	6 A
iK60N 4P 10A C	4P	400 V	C	10 A
iK60N 4P 13A C	4P	400 V	C	13 A
iK60N 4P 16A C	4P	400 V	C	16 A
iK60N 4P 20A C	4P	400 V	C	20 A
iK60N 4P 25A C	4P	400 V	C	25 A
iK60N 4P 32A C	4P	400 V	C	32 A